

# Eaton 259852

Catalog Number: 259852

Eaton Moeller series NZM - Molded Case Circuit Breaker. Remote operator, 380-440VAC, for size 3

General specifications

|                                          |                |
|------------------------------------------|----------------|
| Product Name                             | Catalog Number |
| Eaton Moeller series NZM remote operator | 259852         |
|                                          | EAN            |
|                                          | 4015082598525  |
| Product Length/Depth                     | Product Height |
| 170 mm                                   | 140 mm         |
| Product Width                            | Product Weight |
| 140 mm                                   | 2.8 kg         |
| Compliances                              |                |
| IEC                                      |                |
| RoHS conform                             |                |



## Product specifications

### Used with

N(S)3(-4)

NZM3(-4)

### Type

Accessory Remote operator, can be synchronized

### Special features

Cannot be combined with switch-disconnector PN... M22-CK11(20/02) dual auxiliary switch cannot be combined with NZM3-XR... remote operator

### Voltage rating

380 - 440 V 50/60 Hz

### 10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

### 10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

### 10.2.2 Corrosion resistance

Meets the product standard's requirements.

### 10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

### 10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

### 10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

### 10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

### 10.2.5 Lifting

Does not apply, since the entire switchgear needs to be

## Resources

### Brochures

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

### Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

### Declarations of conformity

[DA-DC-03\\_NZM3](#)

### Drawings

[eaton-circuit-breaker-remote-operator-nzm-remote-operator-dimensions-004.eps](#)

[eaton-circuit-breaker-padlock-nzm-rotary-handle-dimensions.eps](#)

### eCAD model

[ETN.259852.edz](#)

### Installation instructions

[eaton-remote-operator-nzm3-xr-il01208006z.pdf](#)

### Installation videos

[Introduction of the new digital circuit breaker NZM](#)

[The new digital NZM Range](#)

### mCAD model

[DA-CD-nzm3\\_xr](#)

[DA-CS-nzm3\\_xr](#)

### Technical data sheets

[eaton-nzm-technical-information-sheet](#)

evaluated.

#### 10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.7 Inscriptions

Meets the product standard's requirements.

#### 10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.4 Clearances and creepage distances

Meets the product standard's requirements.

#### 10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

#### 10.8 Connections for external conductors

Is the panel builder's responsibility.

#### 10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

#### 10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

#### 10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

#### Frame

NZM3

#### Breaking time

1000 ms

#### Closing delay

80 ms

#### Voltage type

AC

#### Lifespan, mechanical

15000 operations

#### Number of poles

Three-pole/Four-pole

Number of operations per hour - max

60

Voltage tolerance - max

1.1

Voltage tolerance - min

.85

Rated control supply voltage (Us) at AC, 50 Hz - max

440 V

Rated control supply voltage (Us) at AC, 50 Hz - min

380 V

Rated control supply voltage (Us) at AC, 60 Hz - max

440 V

Rated control supply voltage (Us) at AC, 60 Hz - min

380 V

Rated control supply voltage (Us) at DC - max

0 V

Rated control supply voltage (Us) at DC - min

0 V

Rated operating frequency

50 Hz

Signal duration of remote operator at switch off - min

250 ms

Signal duration of remote operator at switch on - min

30 ms

Switch drive type

Motor drive

Terminal capacity (solid/flexible conductor)

0.75 mm<sup>2</sup> - 2.5 mm<sup>2</sup> with ferrule

18 - 14 AWG

Operating voltage - max

1.1 x Us

Operating voltage - min

0.85 x Us

Power consumption

350 VA (110 - 130 V AC)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)