


**SES® end sleeves**  
**Terminals in silvered copper with wide opening**  
**0,5 to 25 mm<sup>2</sup>**



SES®



- Silver plated - for a better conductivity
- Perfect crimping is performed with our crimping tools (see pages D5/5 to 6 of our catalogue).
- Dimensions to **Standard DIN 46228**



type	article number		section mm <sup>2</sup>	dimensions (mm)			
				L	d1	d2	d3
SES 71 S / 6	0710 0001 000	1000	0,5	6	1,0	1,3	2,1
SES 71 / 6	0710 0004 000	1000	0,75	6	1,2	1,5	2,3
SES 72 S / 6	0710 0007 000	1000	1,0	6	1,4	1,7	2,5
SES 72 S / 10	0710 0009 000	1000	1,0	10	1,4	1,7	2,5
SES 72 / 7	0710 0012 000	1000	1,5	7	1,7	2,0	2,8
SES 72 / 10	0710 0014 000	1000	1,5	10	1,7	2,0	2,8
SES 73 / 7	0710 0017 000	1000	2,5	7	2,2	2,5	3,4
SES 73 / 12	0710 0019 000	1000	2,5	12	2,2	2,5	3,4
SES 74 / 9	0710 0022 000	1000	4,0	9	2,8	3,2	4,0
SES 74 / 12	0710 0023 000	1000	4,0	12	2,8	3,2	4,0
SES 75 / 10	0710 0025 000	250	6,0	10	3,5	3,9	4,7
SES 75 / 12	0710 0026 000	250	6,0	12	3,5	3,9	4,7
SES 75 / 15	0710 0027 000	250	6,0	15	3,5	3,9	4,7
SES 76 / 12	0710 0028 000	250	10,0	12	4,5	4,9	5,8
SES 76 / 15	0710 0029 000	250	10,0	15	4,5	4,9	5,8
SES 76 / 18	0710 0030 000	250	10,0	18	4,5	4,9	5,8
SES 77 / 12	0710 0031 000	250	16,0	12	5,8	6,2	7,5
SES 77 / 15	0710 0032 000	250	16,0	15	5,8	6,2	7,5
SES 77 / 18	0710 0033 000	250	16,0	18	5,8	6,2	7,5
SES 78 / 12	0710 0035 000	250	25,0	12	7,3	7,7	9,5
SES 78 / 15	0710 0036 000	250	25,0	15	7,3	7,7	9,5
SES 78 / 18	0710 0037 000	250	25,0	18	7,3	7,7	9,5



• Assortment of end sleeves with crimping tool in blue metal box, with lid

type	article number		contents of the box
<b>Assortment box SK 30 / 4B</b>	0710 0401 000	1	1000 sleeves of each type 71/6 - 72S/6 - 72/7 - and 73/7 1 SES-K 4 crimping tool
<b>Assortment box SK 32 / B</b>	0710 0402 000	1	1000 sleeves of types 71/6 - 72S/6 - and 72/7 500 of types 73/7 - 74/9 - 75/10 250 of type 76/18 and 150 of type 77/18 1 SES-K 3 crimping tool
<b>Assortment box SK 30 / 1B</b>	0710 0405 000	1	1000 sleeves of each type 71/6 - 72S/6 - 72/7 - and 73/7 1 SES-K 1 crimping tool

