



Part Number : [513821500](#)

Product Description : 2.00mm Pitch MicroClasp Wire-to-Board Receptacle Housing, Positive Lock, Single Row, 15 Circuits, White

Series Number : 51382

Status : Active

Product Category : Connector Housings



Documents & Resources

Drawings

[513821500 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[513821500.dxf](#)

Specifications

[561340000-AS-000.pdf](#)

[513829200-200.pdf](#)


[SPK-51382-001-001.pdf](#)

[513820000-PS-001.pdf](#)

[PS-51382-004-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	51382
Description	2.00mm Pitch MicroClasp Wire-to-Board Receptacle Housing, Positive Lock, Single Row, 15 Circuits, White
Application	Signal, Wire-to-Board
Product Name	MicroClasp
UPC	800756632377

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	15
Color - Resin	White
Flammability	94V-0
Gender	Receptacle

Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	681.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
MicroClasp Vertical Single Row Headers	<u>55932</u>
MicroClasp Right-Angle Single Row Headers	<u>55935</u>

Use with Part(s)

Description	Part Number
Pre-Crimped Lead MicroClasp Female-to-MicroClasp Female, Tin (Sn) Plating, 150.00mm Length, 24 AWG, Black	<u>797581001</u>
Pre-Crimped Lead MicroClasp Female-to-MicroClasp Female, Tin (Sn) Plating, 300.00mm Length, 24 AWG, Black	<u>797581002</u>
2.00mm Pitch Crimp Terminal, Female, 28-22 AWG, Copper Alloy, Reel	<u>561349000</u>
2.00mm Pitch Crimp Terminal, Female, 28-22 AWG, Copper Alloy, Bag	<u>561349100</u>
MicroClasp Terminal Position Assurance (TPA) Retainers	<u>500638</u>

