




Temperature cable sensor with screw-in sensor

TS-PT100-SCREW-IN M5/0,5M PUR



Product characteristics

Measuring range	-40...90 °C	-40...194 °F
Process connection	threaded connection M5 external thread	

Application

Special feature	Gold-plated contacts
Measuring element	1 x Pt 100; (to DIN EN 60751, class A)
Installation	surface mount RTD for solid bodies

Electrical data

Protection class	III
------------------	-----

Measuring/setting range

Measuring range	-40...90 °C	-40...194 °F
-----------------	-------------	--------------

Accuracy / deviations

Accuracy	[K]	$\pm (0,15 K + 0,002 x t)$
----------	-----	-----------------------------

Response times

Dynamic response T05 / T09	[s]	3 / 8; (to DIN EN 60751)
----------------------------	-----	--------------------------

Operating conditions

Protection	IP 67
------------	-------

Tests / approvals

Shock resistance	DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	10 g (10...2000 Hz)
MTTF	[years]	11415.5

Mechanical data

Weight	[g]	38.7
Housing	cylindrical	
Design	screw-in sensor	
Materials	stainless steel (316L/1.4404)	
Tightening torque	[Nm]	1.5
Process connection	threaded connection M5 external thread	
Probe diameter	[mm]	4

Remarks

Pack quantity	1 pcs.
---------------	--------

TS9789



Temperature cable sensor with screw-in sensor

TS-PT100-SCREW-IN M5/0,5M PUR

Electrical connection

Cable: 0.5 m, PUR

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

