



Main

Range	New Unica
Accessory / separate part category	Adaptation accessory
Product or component type	Rocker
Number of modules	1 module
Device presentation	Rocker
Fixing mode	Clip-in
Colour tint	Anthracite (RAL 7021)

Complementary


Product destination	Switch with indicator
Surface finish	Matt
Material	Thermoplastic ABS-UV stabilised: rocker PC: visor
Depth	9 mm
Width	22.5 mm
Height	45 mm
Net weight	0.002 kg
Type of packing	Flow-pack
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

IK degree of protection	IK04
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins