
## KEMET Part Number: ALS80A303QT250

(A381UW303M250A)



## ALS80, Aluminum Electrolytic, 30,000 uF, 20%, 250 VDC, -40/+105°C



Dimensions		
D	90mm +/-1mm	
L	220mm +/-2mm	
Т	5.5mm +/-0.5mm	
S	31.8mm +/-0.5mm	
DT	13mm +/-0.5mm	
LT	223.5mm NOM	
TD	10mm MIN	
V	25mm NOM	

Packaging Specifications		
Weight:	2 kg	
Sleeving:	Yes	
Packaging:	Tray	

10mm NOM

Ζ

General Information		
Supplier:	KEMET	
Series:	ALS80	
Dielectric:	Aluminum Electrolytic	
Description:	Screw Terminal, Aluminum Electrolytic	
RoHS:	Yes	
AEC-Q200:	No	
Notes:	Dimensions D And L Include Sleeving. MS (MxH) = M12x16. Mounting Clip (Sold Separately): PYC6045	

Specifications		
Capacitance:	30,000 uF	
Capacitance Tolerance:	20%	
Voltage DC:	250 VDC, 287.5 VDC (Surge)	
Temperature Range:	-40/+105°C	
Rated Temperature:	105°C	
Life:	9000 Hrs (Rated Voltage And Ripple Current At 105C), 15000 Hrs (Rated Voltage At 105C)	
Resistance:	11 mOhms (100Hz 20C), 10 mOhms (10kHz 20C)	
Ripple Current:	26.4 Amps (100Hz 105C), 32.5 Amps (10 kHz 105C)	
Leakage Current:	6000 uA	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

