




Brand of **NTN** corporation

Technical data



6018.EE

Single row deep groove ball bearings



Deep groove ball bearing, radial contact, pressed steel cage, contact seals on both sides

VISUAL (S)



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

Brand	SNR
d - Internal diameter	90 mm
D - External diameter	140 mm
B - Bearing/Inner ring width	24 mm
d1 - External diameter inner ring	104,6 mm
D1 - Inner diameter outer ring	129,6 mm
rs - Min fillet radius	1,5 mm
Radial clearance class	CN
Mass	1,15 kg

PRODUCT PERFORMANCE

C - Dynamic load	61200000 mN
C0 - Static load	50000000 mN
Cu - Fatigue limit load	2100000 mN
f0 - Coefficient	15.7
N lim - Mechanical Limit Speed	16200 °/s
Tmin - Min operating temperature	243,15 °K
Tmax - Max operating temperature	393,15 °K

BEARING FREQUENCIES

BPFO - Over rolling frequency on outer ring (60 rpm)	6.098 Hz
BPFI - Over rolling frequency on inner (60 rpm)	7.902 Hz
BSF - Over rolling frequency on rolling element (60 rpm)	7.629 Hz
BRF - Rotational frequency - rolling element (60 rpm)	3.815 Hz
FTF - Rotational frequency - cage (60 rpm)	0.436 Hz



ABUTMENT

da min - Min shoulder diameter IR	98 mm
da max - Max shoulder diameter IR	104,6 mm
Da max - Max shoulder diameter OR	132 mm
ra max - Max shaft & housing fillet radius	1,5 mm

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$$P = X.F_r + Y.F_a$$

$\frac{f_0 F_a}{C_0}$	e	Fa / Fr ≤ e		Fa / Fr > e	
		X	Y	X	Y
0.172	0.19	1	0	0.56	2.3
0.345	0.22				1.99
0.689	0.26				1.71
1.03	0.28				1.55
1.38	0.3				1.45
2.07	0.34				1.31
3.45	0.38				1.15
5.17	0.42				1.04
6.89	0.44				1

Equivalent static radial load

$$P_0 = X_0.F_r + Y_0.F_a$$

X_0	Y_0
0.6	0.5

For single or DT bearing arrangement :

If $P_0 < F_r$, then use $P_0 = F_r$

