

# Eaton 260156

Catalog Number: 260156

Eaton Moeller series NZM - Molded Case Circuit Breaker. Control circuit terminal, screw connection, NZM 2

General specifications



Product Name

Eaton Moeller series NZM connection  
type

Catalog Number

260156

EAN

4015082601560

Product Length/Depth

21 mm

Product Height

12.5 mm

Product Width

25 mm

Product Weight

0.02 kg

Compliances

IEC  
UL/CSA  
RoHS conform

Certifications

CSA (Class No. 1437-01)  
UL489  
CE marking  
UL (File No. E140305)  
UL listed  
CSA certified  
CSA (File No. 22086)  
UL (Category Control Number DIHS)  
IEC60947  
CSA-C22.2 No. 5-09

## Product specifications

### Used with

NZM2(-4), PN2(-4), N(S)2(-4)

### Type

Accessory Control circuit terminal Terminal

### 10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

### 10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

### 10.2.2 Corrosion resistance

Meets the product standard's requirements.

### 10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

### 10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

### 10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

### 10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

### 10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

### 10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

### 10.2.7 Inscriptions

Meets the product standard's requirements.

### 10.3 Degree of protection of assemblies

## Resources

### Brochures

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

### Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

### Declarations of conformity

[DA-DC-03\\_NZM2](#)

### Drawings

[eaton-circuit-breaker-terminals-nzm-screw-dimensions-002.eps](#)

[eaton-circuit-breaker-terminals-nzm-screw-3d-drawing-002.eps](#)

### eCAD model

[DA-CE-ETN.NZM2-XSTS](#)

### Installation videos

[Introduction of the new digital circuit breaker NZM](#)

[The new digital NZM Range](#)

### mCAD model

[nzm2\\_xsts.stp](#)

[nzm2\\_xsts.dwg](#)

### Technical data sheets

[eaton-nzm-technical-information-sheet](#)

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.4 Clearances and creepage distances

Meets the product standard's requirements.

#### 10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

#### 10.8 Connections for external conductors

Is the panel builder's responsibility.

#### 10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

#### 10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

#### 10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

#### Frame

NZM2

#### Suitable for

Screw connection

Single-pole

#### Number of poles

Three-pole/Four-pole

#### Model

Other

#### Terminal capacity (stranded cable)

0.75 mm<sup>2</sup> - 2.5 mm<sup>2</sup> (1x)

0.75 mm<sup>2</sup> - 1.5 mm<sup>2</sup> (2x)

18 - 14 AWG/kcmil (1x)

18 - 16 AWG/kcmil (2x)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)