

Features

- Medium Duty
- Industrial castor
- Fixed
- Fixing Plate
- Polyurethane
- Corrosion Resistant
- Impact Resistant
- Shock Absorbing

RS PRO Castor Wheels

RS Stock No.: 0730016



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Wheel coated with AVOLAN polyurethane 91 Shore A with aluminium centre. Hub on shielded ball bearings assembled with central spacer. In zinc-chromium plated pressed steel. Assembled with self-locking nut.

General Specifications

Rotation	Fixed
Weight Class	Medium Duty
Load Capacity (Kg)	400
Load Capacity / 4pcs (Kg)	1600
Tyre Material	Polyurethane
Hub Material	Aluminium
Bracket Material	Pressed Steel
Includes Brake	No
Features	Corrosion Resistant, Impact Resistant, Shock Absorbing
Applications	Industrial castor

Operation Environment Specifications

Operating Temperature (Celsius)	-20° to 80°
--	-------------

250x50	200x160	150x115	14x26	302	400	500

Mechanical Specifications

Mounting Type	Single Bolt
Wheel Diameter (mm)	250
Wheel / Tread Width (mm)	50
Overall Height (mm)	302
Number of Fixing Holes	4
Fixing Hole Size (mm)	14x26
Hub Bearing Type	Ball Bearing
Thread Size (M)	
Stem Height (mm)	
Stem Diameter (mm)	
Hardness of Wheel (Shore A)	91
Levelling Extent (mm)	
Offset (mm)	
Castor Weight (Kg)	4.540

Fixing Centres Specifications

Fixing Centres (mm)	150x115
Fixing Centres Length (mm)	150
Fixing Centres Width (mm)	115

Fixing Plate Specifications

Fixing Plate Dimensions (mm)	200x160
Fixing Plate Length (mm)	200
Fixing Plate Width (mm)	160