

LC1F265X7

TeSys F contactor - 3P (3 NO) - AC-3 - ≤ 440 V
265 A - coil 550...600 V AC



Main

| | |
|---|---|
| Range | TeSys |
| Product name | TeSys F |
| Product or component type | Contacteur |
| Device short name | LC1F |
| Contacteur application | Motor control Resistive load |
| Utilisation category | AC-1 AC-3 |
| Poles description | 3P |
| Pole contact composition | 3 NO |
| [Ue] rated operational voltage | ≤ 1000 V AC 50/60 Hz ≤ 460 V DC |
| [Ie] rated operational current | 350 A (≤ 40 °C) at ≤ 440 V AC AC-1 265 A (≤ 55 °C) at ≤ 440 V AC AC-3 |
| Motor power kW | 132 kW at 380...400 V AC 50/60 Hz 140 kW at 415 V AC 50/60 Hz 140 kW at 440 V AC 50/60 Hz 147 kW at 1000 V AC 50/60 Hz 160 kW at 500 V AC 50/60 Hz 75 kW at 220...230 V AC 50/60 Hz 160 kW at 660...690 V AC 50/60 Hz |
| Control circuit type | AC 40...400 Hz |
| Control circuit voltage | 550...600 V AC 40...400 Hz |
| [Uimp] rated impulse withstand voltage | 8 kV |
| Overvoltage category | III |
| [Ith] conventional free air thermal current | 350 A at ≤ 40 °C |
| Irms rated making capacity | 2650 A AC conforming to IEC 60947-4-1 |
| Rated breaking capacity | 2120 kA conforming to IEC 60947-4-1 |
| [Icw] rated short-time withstand current | 2200 A ≤ 40 °C 10 s 1230 A ≤ 40 °C 30 s 950 A ≤ 40 °C 1 min 620 A ≤ 40 °C 3 min 480 A ≤ 40 °C 10 min |
| Associated fuse rating | 315 A aM at ≤ 440 V 400 A gG at ≤ 440 V |
| Average impedance | 0.3 mOhm at 50 Hz - Ith 350 A |
| [Ui] rated insulation voltage | 1000 V conforming to IEC 60947-4-1 1500 V conforming to VDE 0110 group C |
| Power dissipation per pole | 21 W AC-3 37 W AC-1 |
| Mounting support | Plate |
| Standards | EN 60947-1 EN 60947-4-1 IEC 60947-1 IEC 60947-4-1 JEM 1038 |
| Product certifications | BV CCC CSA DNV GL RINA RMRoS UL LROS |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

| | |
|-------------------------|--|
| Connections - terminals | Control circuit : screw clamp terminals 2 cable(s) 1...2.5 mm ² - cable stiffness: flexible - with cable end Power circuit : connector 1 cable(s) 240 mm ² Control circuit : screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 2 cable(s) 1...4 mm ² - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: flexible - with cable end Control circuit : screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: solid - without cable end Control circuit : screw clamp terminals 2 cable(s) 1...4 mm ² - cable stiffness: solid - without cable end Power circuit : lugs-ring terminals 1 cable(s) 240 mm ² Power circuit : bar 2 x (32 x 4 mm) |
| Tightening torque | Power circuit : 35 N.m Control circuit : 1.2 N.m |
| Operating time | 100...170 ms opening 40...65 ms closing |
| Mechanical durability | 10 Mcycles |
| Operating rate | 2400 cyc/h at <= 55 °C |

Complementary

| | |
|---------------------------------|---|
| Control circuit voltage limits | 0.85...1.1 Uc at 55 °C operational 40...400 Hz 0.15...0.2 Uc at 55 °C drop-out 40...400 Hz |
| Inrush power in VA | 650 VA at 20 °C (cos φ 0.9) 40...400 Hz |
| Hold-in power consumption in VA | 10 VA at 20 °C (cos φ 0.9) 40...400 Hz |
| Heat dissipation | 8 W |

Environment

| | |
|---|---|
| IP degree of protection | IP20 front face with shrouds (ordered separately) conforming to IEC 60529 IP20 front face with shrouds (ordered separately) conforming to VDE 0106 |
| Protective treatment | TH |
| Ambient air temperature for operation | -5...55 °C |
| Ambient air temperature for storage | -60...80 °C |
| Permissible ambient air temperature around the device | -40...70 °C |
| Operating altitude | 3000 m without derating in temperature |
| Mechanical robustness | Vibrations contactor open 2 Gn, 5...300 Hz Shocks contactor closed 15 Gn for 11 ms Shocks contactor open 6 Gn for 11 ms Vibrations contactor closed 5 Gn, 5...300 Hz |
| Height | 203 mm |
| Width | 201.5 mm |
| Depth | 213 mm |
| Product weight | 7.44 kg |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Not Green Premium product |
| RoHS | Compliant - since 0843 - Schneider Electric declaration of conformity |
| Product environmental profile | Available |
| Product end of life instructions | Available |