

15EJT1

✓ ACTIVE

Corcom | Corcom EJT


TE Internal #: 2-6609006-5

Power Line, Vertical, 15 A, .250" FASTON Output, 250 VAC,
Filtered, IEC 320/C-14, Corcom EJT, Power Entry Modules

[View on TE.com >](#)



EMI & EMC Solutions > EMI Filters > Power Entry Modules > IEC Filtered Inlets, Corcom EJT Series



Filter Type: **Power Line**
Product Orientation: **Vertical**
Leakage Current (Max) (120VAC, 60Hz): **250 μ A**
Leakage Current (Max) (250VAC, 50Hz): **430 μ A**
Current Rating: **15 A**

[All IEC Filtered Inlets, Corcom EJT Series \(22\)](#)

Features

Product Type Features

Ground Choke Option	No
Filter Type	Power Line
Output Termination Type	.250" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 320/C-14

Electrical Characteristics

Leakage Current (Max) (120VAC, 60Hz)	250 μ A
Leakage Current (Max) (250VAC, 50Hz)	430 μ A
Current Rating	15 A
Operating Voltage	250 VAC

Body Features

Product Orientation	Vertical
---------------------	----------

Mechanical Attachment



Panel Mount Feature Type	Flange
--------------------------	--------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Also in the Series | Corcom EJT



Power Entry Modules(22)

Customers Also Bought




TE Part #4-1879259-3
RP 2B 1K69 0.1% 15PPM CUT LENGTH



TE Part #214803-E
EPSVA KS GD-8 TL 6 3,8 SN *
STROMVERSORG




TE Part #6651214-1
286-0022-12100=CONN,SKT,
CRNEDGE



TE Part #1-1623782-0
SQM5 330R 5% (METAL FILM)



TE Part #2213933-2
SMT TB R/A HEADER, RET, 3.5MM, 2
POS



TE Part #796690-2
TERMI-BLOK PCB MOUNT 2P



TE Part #1-917337-5
DYNAMIC D-3 VERTI. HDR ASSY 2P



TE Part #2-6609006-4
10EJT1=F8136



TE Part #2-1879453-4
TE 1000W 82R 5% Bracket



TE Part #6650384-3
286-0052-12301A=TA CONN,SKT

Documents

Product Drawings

15EJT1=F8137

English

CAD Files

Customer View Model

ENG_CVM_CVM_2-6609006-5_G1.3d_igs.zip

English

Customer View Model



[ENG_CVM_CVM_2-6609006-5_G1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-6609006-5_G1.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE_EJT_SERIES](#)

English

Corcom Combined Selector Charts

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English