

# VIP-PA-50/26/ 2,0M/1756/024 - Front adapter



1162494

<https://www.phoenixcontact.com/in/products/1162494>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VIP VARIOFACE front adapter, with connected system cables for ControlLogix® 1756 I/O. Up to 1 x 8 channels can be connected.

## Your advantages

- Individual I/O modules lock to the controller for connection security
- Integrated lever aids in removal from I/O card
- Marking label can be attached
- Pluggable screw terminals on adapter for Cold Junction Compensation (CJC) connection
- Shield connection: UL Type AWM, Style 1007 18 AWG (0.82 mm<sup>2</sup>) cable, black, 0.5 m length

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1162494                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Product key                          | DK232R                         |
| GTIN                                 | 4063151172879                  |
| Weight per piece (excluding packing) | 636 g                          |
| Country of origin                    | DE                             |

## Technical data

### Product properties

|                |                        |
|----------------|------------------------|
| Product type   | Front adapter          |
| Product family | VARIOFACE Professional |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Pollution degree     | 2  |

### Electrical properties

|                                    |                |
|------------------------------------|----------------|
| Max. permissible operating voltage | 30 V DC        |
| Max. permissible current           | 1 A (per path) |
|                                    | 5 A (CJC)      |

### Supported controller ALLEN-BRADLEY ControlLogix

|                   |            |
|-------------------|------------|
| Suitable I/O card | 1756-IRT8I |
|-------------------|------------|

### Connection data

#### Controller level

|                   |                                         |
|-------------------|-----------------------------------------|
| Connection method | Plug-in connection                      |
| Note              | Can be plugged onto 36-pos. I/O modules |

#### Field level

|                       |                      |
|-----------------------|----------------------|
| Connection method     | IDC/FLK socket strip |
| Number of connections | 1                    |
| Number of positions   | 50                   |
| Pitch                 | 2.54 mm              |

#### Cold Junction Compensation (CJC-0, CJC-1)

|                                  |                                              |
|----------------------------------|----------------------------------------------|
| Connection method                | Push-in / plug connection                    |
| Stripping length                 | 9 mm                                         |
| Conductor cross section rigid    | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Conductor cross section flexible | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Conductor cross section AWG      | 26 ... 16                                    |

### Dimensions

#### Item dimensions

|        |           |
|--------|-----------|
| Width  | 344.98 mm |
| Height | 68.07 mm  |
| Depth  | 56.35 mm  |

#### Cable

|        |     |
|--------|-----|
| Length | 2 m |
|--------|-----|

# VIP-PA-50/26/ 2,0M/1756/024 - Front adapter



1162494

<https://www.phoenixcontact.com/in/products/1162494>

## Cable/line

### 50X0.14 [PVC]

|                                               |                                                                   |
|-----------------------------------------------|-------------------------------------------------------------------|
| UL AWM Style                                  | 2464/1061                                                         |
| Number of positions                           | 50                                                                |
| Shielded                                      | yes                                                               |
| Cable type                                    | 50X0.14 [PVC]                                                     |
| Conductor type                                | Assembled shielded round cable                                    |
| Conductor structure signal line               | 7x 0.16 mm                                                        |
| AWG signal line                               | 26                                                                |
| Conductor cross section                       | 50x 0.14 mm <sup>2</sup>                                          |
| Wire diameter incl. insulation                | 1 mm ±0.03 mm                                                     |
| External cable diameter                       | 11.00 mm ±0.3 mm                                                  |
| Outer sheath, material                        | Semi-rigid PVC                                                    |
| External sheath, color                        | gray                                                              |
| Conductor material                            | Tin-plated Cu litz wires                                          |
| Cable resistance                              | ≤ 145 Ω/km (at 20 °C)                                             |
| Insulation resistance                         | ≥ 20 MΩ*km (20 °C)                                                |
| Smallest bending radius, fixed installation   | 114 mm                                                            |
| Smallest bending radius, movable installation | 205 mm                                                            |
| Dynamic load capacity (bending)               | Max. bending cycles: 5000 (at a radius of ≥ 18x outside diameter) |
| Halogen-free                                  | no                                                                |
| Flame resistance                              | IEC 60332-1-2 (raw cable)                                         |
|                                               | VDE 0842, Part 332-1-2 (raw cable)                                |
|                                               | IEC 60332-3-22 (raw cable)                                        |
|                                               | UL VW-1                                                           |
|                                               | CSA FT-1                                                          |
| Resistance to oil                             | can withstand occasional splashes (raw cable)                     |
| Cable type                                    | Front adapter with cable for one module                           |

## Environmental and real-life conditions

### Ambient conditions

|                                         |                            |
|-----------------------------------------|----------------------------|
| Degree of protection                    | IP20                       |
| Ambient temperature (operation)         | 0 °C ... 60 °C             |
| Ambient temperature (storage/transport) | 0 °C ... 80 °C             |
| Altitude                                | ≤ 2000 m (Above sea level) |
| Permissible humidity (operation)        | ≤ 95 % (non-condensing)    |

## Standards and regulations

|                       |                |
|-----------------------|----------------|
| Standards/regulations | UL 61010-2-201 |
|-----------------------|----------------|

## Notes

|                    |                                                                       |
|--------------------|-----------------------------------------------------------------------|
| Notes on operation | For proper use, the specifications of the installation directive (see |
|--------------------|-----------------------------------------------------------------------|

# VIP-PA-50/26/ 2,0M/1756/024 - Front adapter



1162494

<https://www.phoenixcontact.com/in/products/1162494>

Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.



1162494

<https://www.phoenixcontact.com/in/products/1162494>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1162494>



**UL classified**  
Approval ID: E238705



**cUL Classified**  
Approval ID: E238705



**cUL Recognized**  
Approval ID: E196811



**UL Recognized**  
Approval ID: E196811

**cULus Classified**

**cULus Recognized**

# VIP-PA-50/26/ 2,0M/1756/024 - Front adapter



1162494

<https://www.phoenixcontact.com/in/products/1162494>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27242292 |
| ECLASS-12.0 | 27242292 |
| ECLASS-13.0 | 27242292 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002584 |
|----------|----------|

1162494

<https://www.phoenixcontact.com/in/products/1162494>

Environmental product compliance

|                                         |                                                                                                                                                                                                                                   |
|-----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS                                 |                                                                                                                                                                                                                                   |
| Fulfills EU RoHS substance requirements | Yes                                                                                                                                                                                                                               |
| Exemption                               | 6(c)                                                                                                                                                                                                                              |
| China RoHS                              |                                                                                                                                                                                                                                   |
| Environment friendly use period (EFUP)  | EFUP-50                                                                                                                                                                                                                           |
|                                         | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
| EU REACH SVHC                           |                                                                                                                                                                                                                                   |
| REACH candidate substance (CAS No.)     | Lead(CAS: 7439-92-1)                                                                                                                                                                                                              |
| SCIP                                    | 1759529b-0ef1-4a6c-8951-96e020c066e5                                                                                                                                                                                              |



# VIP-PA-50/26/ 2,0M/1756/024 - Front adapter



1162494

<https://www.phoenixcontact.com/in/products/1162494>

## Accessories

### VIP-2/PT/FLK50/PLC - Passive module

2903803

<https://www.phoenixcontact.com/in/products/2903803>




VARIOFACE interface module, with push-in connection, for 32 channels

---

### VIP-2/SC/FLK50/PLC - Passive module

2315227

<https://www.phoenixcontact.com/in/products/2315227>



VARIOFACE interface module for 32 channels

# VIP-PA-50/26/ 2,0M/1756/024 - Front adapter



1162494

<https://www.phoenixcontact.com/in/products/1162494>

## KME - Cable marker carrier

0807083

<https://www.phoenixcontact.com/in/products/0807083>



Cable marker carrier, white, unlabeled, mounting type: Assembly with cable ties, cable diameter: > 5 mm, text field height: 8 mm, text field width: 20 mm

---

## ZBF10:UNBEDRUCKT - Zack Marker strip, flat

0809997

<https://www.phoenixcontact.com/in/products/0809997>



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, mounting type: latching, for terminal block width: 10 mm, Number of individual labels: 10, text field height: 10 mm, text field width: 5.15 mm

---

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)