

CHARX T2HCI24-3AC32-12,0M2 - Vehicle charging inlet



1358246

<https://www.phoenixcontact.com/in/products/1358246>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX connect universal, AC type 2, Vehicle charging inlet, 32 A , 480 V AC, Single wires, length: 12 m, locking actuator: 24 V, 4-pos., Front and rear mounting, M6, housing: black, for charging electric vehicles (EV) with alternating current (AC), IEC 62196-2, A protective cap is supplied as standard for the AC contacts.

Product description

Vehicle charging inlet for charging with alternating current (AC), compatible with type 2 AC vehicle charging connectors (EVSE), for installation in electric vehicles (EV).

Your advantages

- Complete product range
- Uniform, space-saving dimensions for the installation space and the screw connection points of all Phoenix Contact vehicle charging inlets
- Developed and produced in accordance with the IATF 16949 automotive standard and ISO 9001
- Integrated interlock during charging
- Manual emergency release of the locking actuator
- Protected and sealed against dirt and water with a high degree of protection

Commercial data

Item number	1358246
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	XWCAIC
GTIN	4063151686093
Weight per piece (including packing)	7,266 g
Weight per piece (excluding packing)	7,266 g
Customs tariff number	85444290
Country of origin	PL

CHARX T2HCI24-3AC32-12,0M2 - Vehicle charging inlet



1358246

<https://www.phoenixcontact.com/in/products/1358246>

Technical data

Notes

General	A protective cap is supplied as standard for the AC contacts.
---------	---

Product properties

Product type	Vehicle charging inlet
Product family	CHARX connect universal
Application	for charging electric vehicles (EV) with alternating current (AC) for installation in electric vehicles (EV)
Charging standard	AC type 2
Charging mode	Mode 2, 3
Customer variations	On request

Electrical properties

Type of signal transmission	Pulse width modulation with modulated Powerline communication in accordance with ISO/IEC 15118 / DIN SPEC 70121
Note on the connection method	Crimp connection, cannot be disconnected
Insulation resistance	> 200 MΩ
Coding	4.7 kΩ (between PE and PP)
Temperature monitoring	AC contacts: PTC chain (DIN EN 60738-1)
Type of charging current	AC 3-phase
Charging power	26 kW
Charging current	32 A AC (3-phase)

Power contact

Number	5 (L1, L2, L3, N, PE)
Rated voltage	480 V AC
Rated current	32 A AC

Signal contact

Number	2 (CP, PP)
Rated voltage	30 V AC
Rated current	2 A

Temperature sensors (PTC chain)

Sensor type	PTC chain
Standards/regulations	DIN EN 60738-1
Attachment point	Sensor for the AC contacts
Measuring range_resistance	790.00 Ω ... 1420.00 Ω
Resistance	max. 1280 Ω ±5 K
Recommended measured current	≤ 1 mA (U _{max} = 16 V DC)
Ambient temperature	-40 °C ... 130 °C (Operation)

Locking actuator

CHARX T2HCI24-3AC32-12,0M2 - Vehicle charging inlet



1358246

<https://www.phoenixcontact.com/in/products/1358246>

Locking actuator	24 V, 4-pos.
	Right position
Possible power supply range at the motor	22 V ... 26 V
Maximum voltage for locking detection	30 V
Typical motor current for locking	0.05 A
Reverse current of the motor	max. 0.5 A
Max. dwell time with reverse current	1 s
Recommended adaptation time	600 ms
Pause time after entry or exit path	3 s
Service life insertion cycles	> 10000 load cycles
Lock recognition	available
Mechanical emergency release	available
Ambient temperature (operation)	-30 °C ... 50 °C

Dimensions

Width	73 mm
Height	73 mm
Depth	73 mm

Material specifications

Color (Housing)	black (9005)
Color (Mating face)	black (9005)
Material (Housing)	Plastic
Material (Contact surface)	Silver

Cable/line

Cable length	12 m
Cable type	Single wires

Single-core wires for AC

Cable length	12 m
Cable structure	5 x 6 mm ²
Single wire, material	Silicone
Single wire, color	OG
External cable diameter	15.90 mm ±0.3 mm
Cable resistance	≤ 3.2 Ω/km

Single-core wire for PE

Cable length	12 m
--------------	------

Single-core wires for locking actuator

Cable length	1 m
Cable structure	4 x 0.5 mm ²
Single wire, material	PVC
Single wire, color	BU/RD, BU/GN, BU/YE, BU/BN
External cable diameter	1.60 mm ±0.20 mm

CHARX T2HCI24-3AC32-12,0M2 - Vehicle charging inlet



1358246

<https://www.phoenixcontact.com/in/products/1358246>

Cable resistance	$\leq 37.1 \Omega/\text{m}$
------------------	-----------------------------

Single-core wires for PTC temperature sensors

Cable length	1 m
Cable structure	2 x 0.5 mm ²
Single wire, material	PVC
Single wire, color	BN/GY
External cable diameter	1.60 mm ± 0.20 mm
Cable resistance	$\leq 37.1 \Omega/\text{m}$

Single-core wires for communication

Cable length	1 m
Cable structure	2 x 0.5 mm ²
Single wire, material	PVC
Single wire, color	BK WH
External cable diameter	1.60 mm ± 0.20 mm
Cable resistance	$\leq 37.1 \Omega/\text{m}$

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 10000
Insertion force	< 100 N
Withdrawal force	< 100 N

Environmental and real-life conditions

Ambient conditions

Degree of protection (Vehicle charging inlet)	IP55 (plugged in; when plugged in and ready to operate, the degree of protection is only ensued if both plug-in components are original products from Phoenix Contact or suitable standard-compliant products) IP67 (Inner area of vehicle charging inlet)
Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	4000 m (above sea level)

Standards and regulations

Standards

Standards/regulations	IEC 62196-2
-----------------------	-------------

Mounting

Mounting type	Front and rear mounting (0 to 90 degree frontal inclination possible)
Mounting hole diameter	6.80 mm (ø)
Fixing screws	M6

CHARX T2HCI24-3AC32-12,0M2 - Vehicle charging inlet



1358246
<https://www.phoenixcontact.com/in/products/1358246>

Screws included in the scope of delivery	none
--	------

CHARX T2HCI24-3AC32-12,0M2 - Vehicle charging inlet




1358246

<https://www.phoenixcontact.com/in/products/1358246>

Drawings

Schematic diagram




Block diagram of the locking actuator

CHARX T2HCI24-3AC32-12,0M2 - Vehicle charging inlet

1358246

<https://www.phoenixcontact.com/in/products/1358246>




Operating instructions

CHARX T2HCI24-3AC32-12,0M2 - Vehicle charging inlet

1358246

<https://www.phoenixcontact.com/in/products/1358246>




Locking states of the locking actuator

CHARX T2HCI24-3AC32-12,0M2 - Vehicle charging inlet




1358246
<https://www.phoenixcontact.com/in/products/1358246>

Schematic diagram



Temperature sensor technology resistance range at AC contacts

Dimensional drawing






Dimensional drawing

CHARX T2HCI24-3AC32-12,0M2 - Vehicle charging inlet

1358246

<https://www.phoenixcontact.com/in/products/1358246>

Schematic diagram




Detection for Vehicle Connector

CHARX T2HCI24-3AC32-12,0M2 - Vehicle charging inlet

1358246


<https://www.phoenixcontact.com/in/products/1358246>

Connection diagram



Installation positions

Connection diagram



Pin assignment of vehicle charging inlets

CHARX T2HCI24-3AC32-12,0M2 - Vehicle charging inlet



1358246
<https://www.phoenixcontact.com/in/products/1358246>

Classifications

ECLASS

ECLASS-11.0	27144706
ECLASS-12.0	27144706
ECLASS-13.0	27144706

ETIM

ETIM 9.0	EC002898
----------	----------

CHARX T2HCI24-3AC32-12,0M2 - Vehicle charging inlet



1358246
<https://www.phoenixcontact.com/in/products/1358246>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(c)-I
China RoHS	
Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Disodium 3,3'-[[1,1'-biphenyl]-4,4'-diylbis(azo)]bis(4-aminonaphthalene-1-sulphonate) (C.I. Direct Red 28)(CAS: 573-58-0)
	Lead(CAS: 7439-92-1)
SCIP	7029dbbc-6833-4aba-ad40-99fce9143293

CHARX T2HCI24-3AC32-12,0M2 - Vehicle charging inlet



1358246

<https://www.phoenixcontact.com/in/products/1358246>

Accessories

CHARX T2HI-ELOCK24V - Locking

1331524

<https://www.phoenixcontact.com/in/products/1331524>

CHARX connect universal, Type 2, Locking, Accessories, Single wires, length: 1 m, locking actuator: 24 V, 4-pos., for mounting on vehicle charging inlets, IEC 61851-1



Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in