

## Product information Mechanical risks

### uvex phynomic airLite C ESD//60084



#### Description

A noticeable difference in wearer comfort in Cut Level C: combination of high sensitivity and tactile feel, lightness. The phynomic airLite C ESD is certified according to the DIN EN 16350:2014 (1149-2) standard and is also tested based on the DIN EN 1149-1. Therefore it is perfectly applicable in ESD areas and areas exposed to explosion hazards. You will be equipped for the future with the uvex phynomic airLite C ESD thanks to its touchscreen compatibility for use on all screens, tablets and mobile phones. It is free from accelerators, health protection and skin compatibility dermatologically approved (proDERM®).

#### Characteristics

- 18 Gauge Liner
- anti-static in accordance with EN 16350
- outstanding wearer comfort
- Ergonomic fit
- Flexibility and secure grip
- free from catalysts
- suitable for use with touchscreens
- good breathability
- exceptional dexterity right to the fingertips
- ultra-lightweight
- certified according to Öko-Tex Standard 100

#### Applications

- Work on touchscreen
- ESD areas
- precision assembly work
- For work in antistatic areas
- inspection/maintenance
- precision work
- handling of sharp objects for: assembly, sorting, packaging

EN 388:2016



3X42C



MADE IN GERMANY 

#### Manufacturer

UVEX SAFETY Gloves GmbH & Co. KG  
Elso-Klöver-Str. 6  
21337 Lüneburg  
Postfach 24 47 · 21314 Lüneburg  
GERMANY  
Tel.: +49 4131 9502-0  
Fax: +49 4131 84338  
Email: [gloves@uvex.de](mailto:gloves@uvex.de)  
Website: [uvex-safety.de](http://uvex-safety.de)

Product name	uvex phynomic airLite C ESD
EN	388:2016 (3 X 4 2 C)
Sizes	6, 7, 8, 9, 10, 11, 12
Length approx.	27 cm
Construction	palm and fingers coated, knitted cuff
Basic glove	Dyneema®Diamond Technology 2.0, Polyamid, Elastan, Carbon
Coating	aqua-polymer airLite
Thickness	
Colour	blue/anthracite
Resistance	for dry areas and slightly damp/oily working conditions
Product code	60084