



## 54V XR FLEXVOLT 190mm High Torque Circular Saw – 2 X 6Ah

DCS577T2-QW

Dust blower keeps cut line clear of dust and debris

54V Brushless Motor for increased power and runtime  
General purpose ripping, cross-cutting and bevelling circular saw for wood  
and other construction materials

Quick variable adjustment of bevel angle to 53 degrees

Max Cutting Depth of 65mm at 90 degrees



Sound Power Uncertainty	3 dB(A)
-------------------------	---------

Sound Power	95 dB(A)
-------------	----------

Sound Pressure Uncertainty	3 dB(A)
----------------------------	---------

Sound Pressure	84 dB(A)
----------------	----------

Uncertainty K 1 (Vibration)	1.5 m/s <sup>2</sup>
-----------------------------	----------------------

No Load Speed	5800 Rpm
---------------	----------