

Product data sheet

Specifications



Repacked, residual current circuit breaker (RCCB), Multi9 GFP, 4P, 63A, A-SI type, 30mA

M9R81463W



This repacked option saves 4.746 over the standard condition

Main

Range	Multi9
Product name	Multi9 GFP
Product or component type	Residual current circuit breaker (RCCB)
Device short name	GFP
Device application	Distribution
Poles description	4P
Neutral position	Left
[In] rated current	63 A at 40 °C conforming to EN/IEC 61008-1
Network type	AC
Earth-leakage sensitivity	26 mA conforming to UL 1053 30 mA conforming to EN/IEC 61008-1
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type A-SI (Super Immunised)
Utilisation category	AC-23A conforming to EN/IEC 61008-1
Standards	EN/IEC 61008-1 UL 1053
Product certifications	IEC UL

Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	480Y/277 V AC 60 Hz 415 V AC 50 Hz
Residual current tripping technology	Voltage independent
Rated breaking and making capacity	Idm 1500 A conforming to EN/IEC 61008-1
Rated conditional short-circuit current	I _{nc} 10 kA 100 A gG
[Ui] rated insulation voltage	440 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 61008-1
Contact position indicator	Yes
Control type	Toggle
Local signalling	ON, OFF, fault trip
Mounting mode	Clip-on

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mounting support	DIN rail
9 mm pitches	8
Height	81 mm
Width	72 mm
Depth	60 mm
Product weight	0.45 kg
Colour	Grey
Mechanical durability	20000 cycles
Locking options description	Padlocking in OFF position
Connections - terminals	Tunnel type terminals (top or bottom)1...25 mm² (AWG 18...AWG 3) - flexible Tunnel type terminals (top or bottom)1...35 mm² (AWG 18...AWG 2) - rigid Tunnel type terminals (top or bottom)1...25 mm² (AWG 18...AWG 3) - flexible with ferrule
Wire stripping length	14 mm for top or bottom connection
Tightening torque	3.5 N.m top or bottom

Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3
Electromagnetic compatibility	8/20 µs impulse withstand, 3000 A conforming to EN/IEC 61008-1
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...70 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.200 cm
Package 1 Width	7.700 cm
Package 1 Length	8.500 cm
Package 1 Weight	384.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	27
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	10.650 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

5 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

A7b24ae6-2312-4e67-b7c9-56fce3e8c723

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins