

US-EML (15X6) - Label

0803816

<https://www.phoenixcontact.com/gb/products/0803816>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Label, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0, mounting type: adhesive, Number of individual labels: 132, text field height: 6 mm, text field width: 15 mm



Your advantages

- The markers, which are supplied in uniform sheets, can be marked quickly, easily, and inexpensively
- The US-EML ... UniSheet marking ranges provide markers for identification of equipment in controller, system, and control cabinet building
- The pre-punched labels are easy to separate and can be easily attached
- The sheets provide space for including function descriptions in the project fields
- When used in conjunction with high-quality ink ribbons, they result in a highly resistant form of labeling that is suitable for harsh environments
- A wide range of marker sizes and colors are available for custom designs

Commercial data

Item number	0803816
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG2419
Product key	BG2419
Catalog page	Page 322 (C-3-2019)
GTIN	4055626172460
Weight per piece (including packing)	5.83 g
Weight per piece (excluding packing)	5.83 g
Customs tariff number	39199080
Country of origin	DE

Technical data

Product properties

Product type	Device marking
--------------	----------------

Marking

Number of individual labels	132
Number of individual labels per row	6
Identification technology	Thermal transfer for sheets and cards, UV LED technology

Mounting

Mounting type	adhesive
---------------	----------

Material specifications

Color	white (RAL 9010)
Material	Polyester
Components	free from silicone and halogen

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Dimensions

Width	15 mm
Length	6 mm

Text field

Text field width	15 mm
Text field height	6 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

US-EML (15X6) - Label

0803816

<https://www.phoenixcontact.com/gb/products/0803816>



Classifications

ECLASS

ECLASS-11.0	27281103
ECLASS-12.0	27281103
ECLASS-13.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

US-EML (15X6) - Label

0803816
<https://www.phoenixcontact.com/gb/products/0803816>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk