

FEATURES

- **High Chemical Resistance:** Suitable for a wide range of chemicals, enhancing versatility.
- **Maximum Operating Pressure of 3000 kPa:** Ensures robust performance in demanding applications.
- **Maximum Operating Temperature of 280°C:** Capable of withstanding high-temperature environments.
- **Rotary Speed of 18 m/s:** Supports efficient operation in dynamic systems.
- **8mm Section:** Provides a compact and effective sealing solution.
- **Conforms to ANSI-ESD S20.20:2021, BAM, FDA, RoHS:** Meets key industry standards for safety and compliance.

RS PRO 8mm Polytetrafluoroethylene Gland Packing

RS Stock No: 606-553



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO gland packing is designed for sealing applications in various industrial environments. Made from high-quality polytetrafluoroethylene, it provides excellent chemical resistance and durability. Ideal for use in high-pressure and high-temperature settings, it ensures reliable performance and longevity.

General Specifications

Maximum Operating Pressure	3000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	18 m/s
Section	8 mm
Sub Type	Gland Packing

Mechanical Specifications

Length	8 m
Material	Polytetrafluoroethylene

Operation Environment Specifications

Maximum Operating Temperature	280 °C
-------------------------------	--------

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, BAM, FDA, RoHS
---------------------	--------------------------------------