




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **254 – 404 CMA**

Mating Tab Width: **2.8 mm, 3.18 mm [.11 in, .125 in]**

Features

Product Type Features

Terminates To	Wire & Cable
Wire/Cable Type	Regular Wire
Wire Stop	Yes
Insertion Force	Normal
Sealable	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Electrical Characteristics

Voltage (Max)	600 V
---------------	-------

Body Features

Insulation Material	Nylon
---------------------	-------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	2.8 mm, 3.18 mm[.11 in][.125 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Orientation	Straight



Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Closed

Mechanical Attachment

Mating Retention Type	Dimple
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	2.54 mm[.1 in]
Receptacle Terminal Stock Thickness	.41 mm[.016 in]
Overall Length	18.7 mm[.735 in]
Wire Size	254 – 404 CMA

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

UL Flammability Rating	UL 94V-2
UL Rating	Listed

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece/Carton

Other

Barrel Color	Purple
--------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JUL 2021 (219)



SVHC > Threshold:
Not Yet Reviewed

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 58628-2
PROCIMP DIESET 26-14 ULTRAFast

TE Part # 58628-1
PROCIMP T&D 26-14 ULTRAFast

TE Part # 58052-3
PF UF F-ON SRS 110/125 REC 26-22
DIE SET

Also in the Series | Ultra-Fast 110

Quick Disconnects(14)

Customers Also Bought



TE Part #2-1625892-8
3W SM M/OX 5% 20K

TE Part #293736-1
8 pos. coverpart (kit) for P/N 794617-8

TE Part #1-2600030-0
4CCT BLACK RECEP W/LARGE SEAL

TE Part #62887-1
187 FASTON REC 20-16 AWG TPBR

TE Part #690474-7
SHEAR BLADE

TE Part #2-2600020-2
XRC PIN TERMINAL 14-18AWG Ni Plated

TE Part #1-2176430-4
MPT35 15R 5%

TE Part #NB14664001
VERSAFIT-3X-1-0-SP

TE Part #690482-7
FRONT SHEAR PLATE

Documents

Product Drawings

ULTRAFast 110 ASSY REC 26-22 TPBR LP

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-520366-2_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_7-520366-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-520366-2_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



Ultra-Fast and Ultra Fast Plus

English

Product Specifications

Application Specification

English

Product Environmental Compliance

MD_7-520366-2_12122015149_dmtec

English

MD_7-520366-2_12122015149_dmtec

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Platform Crimping Die Assembly 58052-3

English

Agency Approvals

Agency Approval Document

English