


Data Sheet | Item Number: 294-4032

Lighting connector; push-button, external; without ground contact; 2-pole; Lighting side: for solid conductors; Inst. side: for all conductor types; max. 2.5 mm²; Surrounding air temperature: max 85°C (T85); white

<https://www.wago.com/294-4032>



Color: ■ white



Dimensions in mm

Field-wiring terminal block, 294 Series, white

This field-wiring terminal block (item number 294-4032) is designed for simple and secure connections. Strip lengths must be between 8 and 9 mm when connecting conductors to this field-wiring terminal block. This product features four conductor terminals and utilizes Push-in CAGE CLAMP® and PUSH WIRE®. Push-in CAGE CLAMP® technology provides a universal connection solution for any type of conductor. It allows both solid and fine-stranded conductors with ferrules to be inserted directly into the clamping point without the need for tools. Our PUSH WIRE® connection is the simple and reliable method for connecting solid conductors. The item's dimensions are (20 x 17 x 27.3) mm (width x height x depth). This field-wiring terminal block is suitable for conductor cross sections ranging from 0.5 mm² to 2.5 mm² on one side and for conductor cross sections ranging from 0.5 mm² to 2.5 mm² on the other side as well as conductor cross sections from 0.5 mm² to 2.5 mm² and from 0.5 mm² to 0.75 mm² depending on the conductor type.

Tin is used for coating the contact surfaces.

Electrical data				
Ratings per		IEC/EN 60998-1		
Overvoltage category		III	III	II
Pollution degree		3	2	2
Nominal voltage		-	-	500 V
Rated impulse withstand voltage		-	-	4 kV
Rated current		-	-	24 A
Ratings per		IEC/EN 60998-2-2		
Overvoltage category		III	III	II
Pollution degree		3	2	2
Nominal voltage		-	-	500 V
Rated impulse withstand voltage		-	-	4 kV
Rated current		-	-	24 A
General information				
Wiring direction		Side-entry wiring		
Ratings (note)		Connection points		



Connection Data

Clamping units	10
Total number of potentials	2
Number of connection types	4
PE function	without PE contact

Connection 1	
Connection type	External 1
Connection technology	Push-in CAGE CLAMP®
Number of connection points	2
Actuation type	Push-button
Connectable conductor materials	Copper
Solid conductor	0.5 ... 2.5 mm² / 18 ... 12 AWG
Solid conductor; push-in termination	0.5 ... 2.5 mm² / 18 ... 12 AWG
Stranded conductor	0.5 ... 2.5 mm² / 18 ... 14 AWG
Fine-stranded conductor	0.5 ... 2.5 mm² / 18 ... 14 AWG
Fine-stranded conductor; with insulated fer- rule	0.5 ... 1.5 mm² / 18 ... 16 AWG
Fine-stranded conductor; with uninsulated ferrule	0.5 ... 1.5 mm² / 18 ... 16 AWG
Fine-stranded conductor; with ferrule; push- in termination	0.5 mm² / 18 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches
Pole number	2
Wiring direction	Side-entry wiring

Connection 2	
Connection type	Internal 2
Connection technology	PUSH WIRE®
Number of connection points	1
Actuation type	Push-in
Solid conductor	0.5 ... 2.5 mm² / 18 ... 14 AWG
Fine-stranded conductor; with insulated fer- rule	0.5 ... 1 mm² / 18 ... 16 AWG
Fine-stranded conductor; with uninsulated ferrule	0.5 ... 1.5 mm² / 18 ... 14 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches

Connection 3	
Connection type	Internal 3
Connection technology	PUSH WIRE®
Number of connection points	1
Actuation type	Push-in
Solid conductor	0.5 ... 1.5 mm² / 18 ... 16 AWG
Fine-stranded conductor; with insulated fer- rule	0.5 ... 0.75 mm² / 18 AWG
Fine-stranded conductor; with uninsulated ferrule	0.5 ... 1 mm² / 18 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches

Connection 4	
Connection type	Internal 4
Connection technology	PUSH WIRE®
Number of connection points	1
Actuation type	Push-in
Solid conductor	0.5 ... 0.75 mm² / 18 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches

Physical data	
Pin spacing	10 mm / 0.394 inches
Width	20 mm / 0.787 inches
Height	17 mm / 0.669 inches
Depth	27.3 mm / 1.075 inches



Mechanical data		
Marking		DA- DA+
Mounting type		without snap-in mounting feet

Material data		
Note (material data)		Information on material specifications can be found here
Color		white
Material group		IIIa
Insulation material (main housing)		Polycarbonate (PC)
Flammability class per UL94		V0
Clamping spring material		Chrome-nickel spring steel (CrNi)
Contact material		Electrolytic copper (E _{Cu})
Contact Plating		Tin
Fire load		0.093 MJ
Halogen-free		Yes
Weight		6.1 g

Environmental requirements		
Temperature stability		120 °C
T marking		T85

Commercial data		
Product Group		8 (Misc. Chassis Mount Blocks)
PU (SPU)		1000 pcs
Packaging type		Foil
Country of origin		CH
GTIN		4050821097730
Customs tariff number		85369010000

Product Classification		
UNSPSC		39121409
eCl@ss 10.0		27-14-11-06
eCl@ss 9.0		27-14-11-06
ETIM 9.0		EC001284
ETIM 10.0		EC001284
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption
SCIP notification number (Austria)		41386470-7443-4075-8be2-93319fd061c3
SCIP notification number (Belgium)		872b1208-6def-4389-ae1d-48b0a8c9fa4f
SCIP notification number (Bulgaria)		cb7dd632-f56e-4352-b7e7-66f809d94eba
SCIP notification number (Czech Republic)		06ade38b-c9d1-4717-b8e5-e64f44eecfbe
SCIP notification number (Denmark)		aafe92df-1507-4a83-a55e-2cd912dc3840
SCIP notification number (Finland)		bafa3fb1-32fc-452f-bcee-28ea5dd61532
SCIP notification number (France)		4362e940-d406-4d1f-9b17-1b3e752e2141
SCIP notification number (Germany)		a4abbef0-aac8-443f-8131-5456c589fad4
SCIP notification number (Hungary)		afdb5ac3-124e-432b-9875-3441bf574753
SCIP notification number (Italy)		0176a0a4-7325-4763-9143-c78b2b472519
SCIP notification number (Netherlands)		4f4ca581-c5a5-419b-a977-e309b70f6dd0
SCIP notification number (Poland)		b2522616-6a7b-4dcb-b3f5-6c4c8e2d6a2b
SCIP notification number (Romania)		1223226d-5e25-4564-a07b-6bc522518645

Environmental Product Compliance	
SCIP notification number (Sweden)	6e5e15b7-e7f4-4772-a957-f00378e7b4f8

Approvals / Certificates

General approvals		Declarations of conformity and manufacturer's declarations
		
Approval	Standard	Certificate Name
ENEC 05 DEKRA Certification B.V.	EN 60998	2128791.01
		EU-Declaration of Conformity WAGO GmbH & Co. KG
		UK-Declaration of Conformity WAGO GmbH & Co. KG

Downloads

Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 294-4032	

Documentation

Bid Text			
294-4032	19.02.2019	xml 5.58 KB	
294-4032	13.06.2017	doc 27.00 KB	

CAD/CAE-Data

CAD data	CAE data
2D/3D Models 294-4032 	WSCAD Universe 294-4032 
	ZUKEN Portal 294-4032 

1 Compatible Products

1.1 Optional Accessories

1.1.1 Strain relief

1.1.1.1 Strain relief

Item No.: 294-370
Strain relief; for 294 Series; with snap-in mounting feet; white

Item No.: 294-375
Strain relief; for 294 Series; without snap-in mounting feet; white

1.1.1.2 Strain relief plate

Item No.: 294-364
Strain relief plate; for 294 Series; for multi-core cables; 3- to 5-pole; with secured clamp; white

Item No.: 294-384
Strain relief plate; for 294 Series; for single strands; 3- to 5-pole; with secured clamp; white

1.1.2 Tool

1.1.2.2 Operating tool

Item No.: 206-294
Disconnection tool; green

Installation Notes

Installation

2-pole – without ground contact

Mounting hole for screw
Notice: The maximum thread diameter for self-tapping screws is 3 mm.

Hole for screw mount
Notice: The maximum thread diameter for self-tapping screws is 3 mm.

Conductor termination


EUROPE
1 x 0.5 ... 2.5 mm² "s"
1 x 0.5 ... 1.5 mm² "s"
1 x 0.5 ... 0.75 mm² "s"
AMERICA
1 x AWG 18 ... 14 "s"
1 x AWG 18 ... 16 "s"
1 x AWG 18 "s"
JAPAN
1 x 0.8 ... 1.6 mm diam. "s"
1 x 0.8 ... 1 mm diam. "s"
1 x 0.8 mm diam. "s"

Internal connection:
PUSH WIRE® for internal wiring with solid conductors

EUROPE
2 x 0.5 ... 2.5 mm² "s, str, f-str"
AMERICA
2 x AWG 18 ... 12 "s"
2 x AWG 18 ... 14 "s, f-str"
JAPAN
2 x 0.8 ... 2 mm diam. "s"
2 x 0.5 ... 2 mm² "str, f-str"

External connection:
Push-in CAGE CLAMP® for field-wiring with all conductor types

Conductor termination



Terminating five conductors per pole – solid and fine-stranded.

