




Connectors > D-Shaped Connectors > Microminiature & Nanominiature D Connectors > NANONICS DUALOBE Connector: Receptacle, Plastic Shell



Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **9**

Centerline (Pitch): **.64 mm [ .025 in ]**

Sealable: **No**

[All NANONICS DUALOBE Connector: Receptacle, Plastic Shell \(13\)](#)

Features

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	9
---------------------	---

Contact Features

Contact Type	Socket
Contact Options	Installed

Termination Features

Termination Method to PCB	Surface Mount
Termination Method to Wire & Cable	Preterminated Flying Leads

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	.64 mm[.025 in]
--------------------	-----------------



Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (40% in 74023047) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts







Customers Also Bought




TE Part #1045672-1  
1062 0000 00




TE Part #1375799-1  
ASSY, 120 POS PC104 PLUS




TE Part #2000713-7  
RA Keyed Guide Mod, Vita 46, Machined




TE Part #5-147278-3  
04 MTE HDR SRRA SFMNT .100CL




TE Part #1625971-7  
HSA25 120R 5%




TE Part #5-103669-2  
03 MTE HDR SRST LATCH W/HLDWN




TE Part #146888-1  
1FHP,64,30A/P,S,C,S10,12,13,15



TE Part #2085945-7  
QSFP+ Assy, 2x1, Gskt, 4LP-All, Sn EONs



TE Part #2102870-1  
DC, 7Row, Right End, MULTIGIG RT 2R



TE Part #60824-1  
.058 DIA PIN PC PTPPHBZ

Documents

Product Drawings  
SSL009L2HN = SMT CONN

English

CAD Files  
3D PDF  
3D  
Customer View Model  
ENG\_CVM\_CVM\_1589462-9\_T\_c-1589462-9-t.2d\_dxf.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_1589462-9\_T\_c-1589462-9-t.3d\_igs.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_1589462-9\_T\_c-1589462-9-t.3d\_stp.zip  
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



[Datasheets & Catalog Pages](#)  
[1589462 Nanonics Cross Reference](#)  
[English](#)