





















- Standard hood
- Corrosion-resistant hood (series K)



Side bayonet on hood

Style	Ordering number	Cable entry			Description	Outline drawing dimensions in mm	
		 PG	 PG	 PG			
Hood top entry	42.32.06.05 42.32.06.79 42.32.06.69	16	16	16	HB.6.STS.1.16 HB.6.STS.1.16.Z HB.6.STS.1.16.G		
	51.42.32.06.05 51.42.32.06.79 51.42.32.06.69	16	16	16	HB-K.6.STS.1.16 HB-K.6.STS.1.16.Z HB-K.6.STS.1.16.G		
high construction	49.32.16.07 49.32.16.80 49.32.16.70 49.32.16.09 49.32.16.81 49.32.16.71	21 21 29 29	21 21	21 29	HD.16.STS.1.21 HD.16.STS.1.21.Z HD.16.STS.1.21.G HD.16.STS.1.29 HD.16.STS.1.29.Z HD.16.STS.1.29.G		
	51.49.32.16.07 51.49.32.16.80 51.49.32.16.70 51.49.32.16.09 51.49.32.16.81 51.49.32.16.71	21 21 29 29	21 21	21 29	HD-K.16.STS.1.21 HD-K.16.STS.1.21.Z HD-K.16.STS.1.21.G HD-K.16.STS.1.29 HD-K.16.STS.1.29.Z HD-K.16.STS.1.29.G		
top entry standard construction	42.30.06.05 42.30.06.79 42.30.06.69	16	16	16	HB.6.STO.1.16 HB.6.STO.1.16.Z HB.6.STO.1.16.G		
	51.42.30.06.05 51.42.30.06.79 51.42.30.06.69	16	16	16	HB-K.6.STO.1.16 HB-K.6.STO.1.16.Z HB-K.6.STO.1.16.G		
high construction	49.30.16.07 49.30.16.80 49.30.16.70 49.30.16.09 49.30.16.81 49.30.16.71	21 21 29 29	21 21	21 29	HD.16.STO.1.21 HD.16.STO.1.21.Z HD.16.STO.1.21.G HD.16.STO.1.29 HD.16.STO.1.29.Z HD.16.STO.1.29.G		
	51.49.30.16.07 51.49.30.16.80 51.49.30.16.70 51.49.30.16.09 51.49.30.16.81 51.49.30.16.71	21 21 29 29	21 21	21 29	HD-K.16.STO.1.21 HD-K.16.STO.1.21.Z HD-K.16.STO.1.21.G HD-K.16.STO.1.29 HD-K.16.STO.1.29.Z HD-K.16.STO.1.29.G	