

[→ Honeywell.com](#) [→ Automation & Control Solutions](#)[HOME](#)[ABOUT US](#)[PRODUCTS & INFORMATION](#)[NEWS & EVENTS](#)[SALES & SUPPORT](#)[LOGIN](#)

Honeywell Sensing and Control



Search



3455RC 01000226 Thermostats

(Home : Products)

narrow your search

Products

- Controls Monitoring and Lighting (354)
- Machine Safety (1726)
- Sensors (7056)
- Switches (9789)

Technology

- Control and Instrumentation (1063)
- Electromechanical (9332)
- Microstructure (2317)
- Optical/Infrared (1077)
- Thick Film (1764)
- More...

**3455RC Redi-Temp Series Ceramic Automatic Reset Thermostats**

Actual product appearance may vary.

[Sales & Service](#)[Distributor Inventory](#)

Need Help?

[Click here to contact us](#)[Overview](#)[Specs](#)[Documentation](#)[Application Notes](#)

Description

Shipped from stock, the 3455RC Series thermostats are often suitable for applications such as copy machines, power supplies, telecommunications and ovens. UL, CSA and European approval agencies listings available.

Features

Features

Cost effective
Rivet sleeve construction
High profile
High temperature
High current

Product Specifications

Functional Properties
Reset Type
Amperage
Voltage
Operating Temperature
Environmental Exposure Range
Open Temperature
Close Temperature
Open Tolerance
Close Tolerance
Dielectric Strength
Insulation Resistance
Contact Resistance
Housing Material
Contact Material
Agency Approvals and Standards
Mounting
Series Name

None Available



Application Note Library

Potential Applications

Potential Applications

Copy machines
Power supplies
Telecommunications
Office copy machines
Ovens

Open on rise
Automatic
15 A/10 A resistive max.
120 Vac/240 Vac
0 °C to 260 °C [32 °F to 500 °F]
-20 °C to 287 °C [0 °F to 550 °F]
51.7 °C [125 °F]
35.0 °C [95 °F]
2.8 °C [5 °F]
4.4 °C [8 °F]
MIL-STD-202, Method 301; 2000 Vac 60 Hz - Terminal to Case
MIL-STD-202, Method 302; 500 MOhm
MIL-STD-202, Method 307; 0.050 Ohm max.
Ceramic
Silver/nickel alloy
UL, CSA, VDE
B203S moveable bracket
3455RC