

Specifications



Photo is representative



Eaton DX1-343D3FB-C21CE

Eaton PowerXL DX1 High Performance Frequency inverter, Three-phase, 500 V, 4.3 A, 1.1 kW/1.5 kW, EMC Filter & DC-Choke, Brake chopper, LCD, IP21, NEMA 1

General Specifications

PRODUCT NAME	Eaton PowerXL DX1 Variable frequency drives
CATALOG NUMBER	DX1-343D3FB-C21CE
PRODUCT LENGTH/DEPTH	237.4 mm
PRODUCT HEIGHT	327 mm
PRODUCT WIDTH	153 mm
PRODUCT WEIGHT	7 kg
CERTIFICATIONS	CE
CATALOG NOTES	The brake resistors are assigned based on the maximum rated power of the variable frequency drive. Additional brake resistors and designs (e.g. different duty cycles) are available upon request.
UPC	786689830656
MODEL CODE	DX1-343D3FB-C21CE

Product specifications

BRAKE CHOPPER	Brake chopper
FRAME SIZE	FR1
PHASE	Three-phase
VOLTAGE RATING	440/480 V
COMMUNICATION	• Modbus RTU • Modbus TCP • Bluetooth
ENCLOSURE	IP21
SERIES	P0600
KEYPAD	Membrane Keypad
DISPLAY	LCD
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.

Resources

BROCHURES	eaton-powerxl-dx1-vfd-brochure-br040026en-us.pdf
CATALOGUES	eaton-drives-soft-starter-catalog-ca04020001zen-us.pdf
FLYERS	eaton-powerxl-dx1-vfd-flyer-fl040007en-us.pdf
MANUALS AND USER GUIDES	eaton-fiber-card-manual-mn040076en-us.pdf
	eaton-abz-card-user-manual-mn040075en-us.pdf
	eaton-dx1-app-manual-mn040069en-us.pdf
	eaton-dx1-io-options-card-user-manual-mn040079en-us.pdf
	eaton-dual-port-eip-communication-manual-mn040077en-us.pdf
	eaton-powerxl-dx1-communication-manual-mn040071en-us.pdf
	powerxl-dx1-vfd-installation-manual-mn040068en.pdf
	eaton-powerxl-dx1-dxx-ext-sabz-dxx-ext-fs-mn040070en-us.pdf
	eaton-powerxl-dx1-safety-tool-mn040074en-us.pdf
	eaton-powerxl-vfd-profinet-manual-mn040062en-us.pdf
	eaton-power-xpert-incontrol-mn040013en-us.pdf
SOFTWARE, FIRMWARE, AND APPLICATIONS	eaton-powerxl-dx1-profinet-gsdml-v244.zip

10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
AMBIENT OPERATING TEMPERATURE - MAX	50 °C
AMBIENT OPERATING TEMPERATURE - MIN	-10 °C
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MAX	50 °C
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MIN	-30 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
ASSIGNED MOTOR CURRENT IM AT 400 V, 50 HZ, 110% OVERLOAD	3.6 A
ASSIGNED MOTOR CURRENT IM AT 400 V, 50 HZ, 150% OVERLOAD	2.6 A

RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE	10 %
RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE	10 %
RATED OPERATIONAL POWER AT 500 V, 50 HZ, 3-PHASE, 110% OVERLOAD	2.2 kW
SWITCH-ON THRESHOLD FOR THE BRAKING TRANSISTOR	850 VDC
VOLTAGE RATING - MAX	500
ASSIGNED MOTOR CURRENT IM AT 440 - 480 V, 60 HZ, 150% OVERLOAD	1.5 A
ASSIGNED MOTOR CURRENT IM AT 440/480 V, 60 HZ, 110% OVERLOAD	2 A
ASSIGNED MOTOR CURRENT IM AT 500 V, 50 HZ, 110% OVERLOAD	4 A
ASSIGNED MOTOR CURRENT IM AT 500 V, 50 HZ, 150% OVERLOAD	2.9 A
ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ	1.5 HP
ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 110% OVERLOAD	2 HP
BRAKING RESISTANCE	63 Ω
INPUT CURRENT ILN AT 110% OVERLOAD	4 A
INPUT CURRENT ILN AT 150% OVERLOAD	3.1 A
MAINS CURRENT DISTORTION	35.3 %
MAINS VOLTAGE - MAX	500 V
MAINS VOLTAGE - MIN	380 V
NOMINAL OUTPUT CURRENT I2N	4.3 A
NUMBER OF HW- INTERFACES (INDUSTRIAL ETHERNET)	1
NUMBER OF HW- INTERFACES (OTHER)	1
NUMBER OF HW-	0

INTERFACES (PARALLEL)	
NUMBER OF HW-INTERFACES (RS-232)	0
NUMBER OF HW-INTERFACES (RS-422)	0
NUMBER OF HW-INTERFACES (RS-485)	1
NUMBER OF HW-INTERFACES (SERIAL TTY)	0
NUMBER OF HW-INTERFACES (USB)	0
NUMBER OF INTERFACES (PROFINET)	2
NUMBER OF OUTPUTS (ANALOG)	2
OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX	1.1 kW
OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX	1.5 kW
OUTPUT FREQUENCY - MAX	400 Hz
OUTPUT VOLTAGE - MAX	500 V
OVERLOAD CURRENT IL AT 110% OVERLOAD	4.73 A
OVERLOAD CURRENT IL AT 150% OVERLOAD	4.95 A
RATED FREQUENCY - MAX	66 Hz
RATED FREQUENCY - MIN	45 Hz
RATED OPERATIONAL CURRENT (IE) AT 110% OVERLOAD	4.3 A
RATED OPERATIONAL CURRENT (IE) AT 150% OVERLOAD	3.3 A
AIR VOLUME CAPACITY	24 m³/h
ALTITUDE	Max. 1000 m Max. 3000 m Above 1000 m with 1 % derating per 100 m Max. 2000 m for Corner Grounded TN Systems
PROTECTION	Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)
RESOLUTION	0.01 Hz (Frequency resolution, setpoint value)
APPLICATION IN	Yes

DOMESTIC AND COMMERCIAL AREA PERMITTED	
APPLICATION IN INDUSTRIAL AREA PERMITTED	Yes
BRAKING TORQUE	Adjustable to 150 % (I/Ie), DC - Main circuit Max. 30 % MN, Standard - Main circuit Adjustable to 150 %, DC - Main circuit Max. 100 % of rated operational current Ie with external braking resistor - Main circuit
CABLE LENGTH	100 m, screened, maximum permissible, Motor feeder C3 ≤ 50 m, Radio interference level, maximum motor cable length C2 ≤ 10 m, Radio interference level, maximum motor cable length
CLIMATIC PROOFING	< 95 average relative humidity (RH), no condensation, no corrosion
COMMUNICATION INTERFACE	Modbus RTU, built in Modbus TCP, built in Ethernet IP, built in Ethernet IP dual port, optional PROFIBUS, optional PROFINET, optional
CONVERTER TYPE	U converter
DEGREE OF PROTECTION	NEMA 1 IP21
EFFICIENCY	98.10%
ELECTROMAGNETIC COMPATIBILITY	1st and 2nd environments (according to EN 61800-3)
ENVIRONMENTAL CLASS	3C2, 3S2 (Air quality)
FEATURES	Parameterization: Fieldbus Parameterization: Keypad Parameterization: Power Xpert inControl Tool-less swapping of fan Temperature-controlled fan
FITTED WITH:	Internal DC link Brake chopper

	Multi-line graphic display DC link choke IGBT inverter Radio interference suppression filter Additional PCB protection Breaking resistance Control unit PC connection
FRAME SIZE	FS1
FUNCTIONS	4-quadrant operation possible, Closed loop control with Encoder feedback, extended Safety functions with Option board
LEAKAGE CURRENT AT GROUND IPE - MAX	2.9 mA
MAINS SWITCH-ON FREQUENCY	Maximum of one time every 60 seconds
MOUNTING POSITION	Vertical
NUMBER OF INPUTS (ANALOG)	2
NUMBER OF INPUTS (DIGITAL)	6
NUMBER OF OUTPUTS (DIGITAL)	1
NUMBER OF PHASES (INPUT)	3
NUMBER OF PHASES (OUTPUT)	3
NUMBER OF RELAY OUTPUTS	2 (parameterizable, 2 changeover contacts, 6 A (240 V AC) / 6 A (30 V DC))
NUMBER OF SLOTS	4 (expansion)
OPERATING MODE	Closed loop speed control (CL) Closed Loop Torque control (CLT) Sensorless vector control (SLV) Speed control with slip compensation Torque regulation V/f control
OVERVOLTAGE CATEGORY	III
POLLUTION DEGREE	2
POWER CONSUMPTION	2771 W
PROTOCOL	Other bus systems
RADIO INTERFERENCE CLASS	C1: with external filter, for conducted emissions only

	C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary. Optional external radio interference suppression filter for longer motor cable lengths and for use in different EMC environments
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	100 kA
RATED CONTROL SUPPLY VOLTAGE	internal, 10 V DC (Us, max. 10 mA) for analog references, 24 V DC external supply Uc
RATED CONTROL VOLTAGE (UC)	24 V DC (external, max. 250 mA options incl.)
SAFETY FUNCTION/LEVEL	STO (Safe Torque Off, SIL3, PLe Cat 4), SS1, SBC, SLS, SSM, SLA, SSR, SAR (SIL3, PLe, Cat 3), SOS, SS2, SDI (SIL2, PLc, Cat 2)
SHOCK RESISTANCE	Mechanical, According to EN 61800-5-1, IEC/EN 60068-2-27 UPS drop test (for weights inside the UPS frame) Storage and transportation: maximum 15 g, 11 ms (inside the packaging)
SHORT-CIRCUIT PROTECTION RATING	10 A, UL (Class CC or J), Safety device (fuse or miniature circuit-breaker), Power Wiring
STARTING CURRENT - MAX	200 %, IH, max. starting current (High Overload), For 2 seconds every 20 seconds, Power section
SUITABLE FOR	Branch circuits, (UL/CSA)
SUPPLY FREQUENCY	50/60 Hz
SWITCHING FREQUENCY	4 kHz, 1 - 12 kHz adjustable, PWM, Power section, Main circuit
SYSTEM CONFIGURATION TYPE	TN-S TN-C TN-C-S TT IT

VIBRATION

Vibration according to EN 61800-5-1, IEC/EN 60068-2-6: 10 – 150 Hz, displacement amplitude 0.075 mm at 10 Hz to 57 Hz, maximum acceleration amplitude: 1 g at 57 Hz to 150 Hz

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

