

MARTINDALE
ELECTRIC

Specification
FL30
Lamp Tester



ELECTRICAL SPECIFICATIONS

Lamp test voltage: 3kV at 280kHz approx
(with new battery)

Field strength: 100 μ V/m approx.

GENERAL SPECIFICATIONS

Operating environment: -10°C to 50°C \leq
70% R.H.

Altitude: up to 2000m

Power: Single standard 9 volt battery, IEC
6LR61, NEDA 1604

Dimensions: 169 x 40 x 24 mm approx.

Weight: 109g (battery included) approx.

Includes: Carry case, telescopic antenna,
9V battery, instructions.

SAFETY

Conforms to BS EN61010-1 CAT I
max 50V to earth

Pollution Degree: 2

EMC: Conforms to BS EN61326