

# G-INS-N3/8-S68L-PNES-BK - Cable gland



1411156

<https://www.phoenixcontact.com/in/products/1411156>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, material for screw connection: PA, application: Standard, external cable diameter 5 mm ... 10 mm, shielding: no, connecting thread: 3/8" NPT, color: jet black RAL 9005

## Your advantages

- Plastic material conforms to UL 746C f1

## Commercial data

Item number	1411156
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF7
Product key	AF7DCX
Catalog page	Page 684 (C-4-2015)
GTIN	4046356922920
Weight per piece (including packing)	10.6 g
Weight per piece (excluding packing)	10.16 g
Customs tariff number	39269097
Country of origin	TR

# G-INS-N3/8-S68L-PNES-BK - Cable gland



1411156

<https://www.phoenixcontact.com/in/products/1411156>

## Technical data


### Mounting

Assembly note	1) Mount screw connection support in the housing using the correct torque 2) Insert cable 3) Tighten union nut using the correct torque
---------------	---

### Product properties

Product type	Cable screw gland
Application	Standard
No. of conductors	1
Manufacturer	BIMED
Manufacturer Designation	BSPA-21
Shielded	no

### Dimensions

Dimensional drawing	
Length	44 mm
Length of the connecting thread	15 mm
Wrench size, union nut	22 mm
Wrench size, support	22 mm
Hexagon angular dimension	25 mm
Thread type connection side	3/8" NPT

### Connection data

Tightening torque	2 Nm $\pm$ 0.5 Nm (Cap nut)
	1 Nm (Support sleeve)

### Material specifications

Color	black (RAL 9005)
Material Housing	PA (Housing)
Flammability rating according to UL 94	V2
Seal material Cable seal	CR
Material for screw connection	PA

### Cable/line

External cable diameter	5 mm ... 10 mm
	5 mm ... 10 mm (for UL 514 B)
Halogen-free	no

# G-INS-N3/8-S68L-PNES-BK - Cable gland



1411156

<https://www.phoenixcontact.com/in/products/1411156>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP68 (5 bar / 0.5 h)
	IP66
Ambient temperature (operation)	-40 °C ... 100 °C (static)

# G-INS-N3/8-S68L-PNES-BK - Cable gland


1411156

<https://www.phoenixcontact.com/in/products/1411156>



## Drawings

Dimensional drawing



# G-INS-N3/8-S68L-PNES-BK - Cable gland



1411156

<https://www.phoenixcontact.com/in/products/1411156>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1411156>



**cUL Recognized**

Approval ID: E199260



**UL Recognized**

Approval ID: E199260

**cULus Recognized**

# G-INS-N3/8-S68L-PNES-BK - Cable gland



1411156

<https://www.phoenixcontact.com/in/products/1411156>

## Classifications

### ECLASS

ECLASS-11.0	27144432
ECLASS-12.0	27140801
ECLASS-13.0	27140801

### ETIM

ETIM 9.0	EC000441
----------	----------

### UNSPSC

UNSPSC 21.0	39121300
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

# G-INS-N3/8-S68L-PNES-BK - Cable gland

1411156

<https://www.phoenixcontact.com/in/products/1411156>



## Accessories

### A-INL-NPT3/8-P-BK - Counter nut

1411236

<https://www.phoenixcontact.com/in/products/1411236>

Counter nut, for threads 3/8"-NPT, color: jet black RAL 9005



---

### SEALING PLUG 8X16 RD - Sealing plug

1400257

<https://www.phoenixcontact.com/in/products/1400257>

Sealing plug, color: red



---

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.  
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420  
[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)