

Backpack Vacuum Cleaner XGT®

VC012G

40Vmax Brushless AWS

Model VC012G is a cordless backpack cleaner powered by 40Vmax XGT® Li-Ion battery (two in parallel or one).

Feature and Benefits: Suction power adjustment: 3 modes. AWS.



Technical specifications

Vacuum hose length	1,5 m
Vacuum hose diameter	28 mm
Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Air volume	2,1 m³/min
Max. sealed suction	200 mbar
Suction power	45 / 85 / 180 W
Automatic Filter Cleaning System	✓
AWS ready	✓
Continuous Use XGT® 40V Max / 5.0 Ah X2	130 / 75 / 40 min
Dust Bag Capacity	5,5 - 6,0 L
Sound Pressure Level (L _{pA})	≤ 70 dB(A)
Product net weight	5,7 kg
Noise Uncertainty (K Factor)	2,5 dB(A)
Tool weight with battery	6,4 - 9,5 kg

User benefits

- Low noise level for pleasant work.
- 3 modes for suction power with mode memory function
- HEPA Filter is used to capture very fine particles effectively

Link to product - www.makitauk.com



Related products

Optional AC

191C26-2
Dust bag, fleece



191Y84-0
Dust Bag Set



417765-1
Adapter 22 mm



424379-9
Front Cuff Ø24mm



A-34235
Hose Ø 28 mm x 1.5 m



Other

User manual

Parts drawing