




TE Internal #: 2484144-1
Receptacle Contact, Gold Flash, 50 VAC, 50 VDC, 1.3mm Contact Size, 28 – 30 AWG, .081 – .0127 mm² Wire, 159.8 CMA, Crimp, Copper Nickel Tin

[View on TE.com >](#)

Connectors > Contacts > Connector Contacts



Contact Type: **Receptacle**
Contact Mating Area Plating Material: **Gold Flash**
Wire Contact Termination Area Plating Material: **Tin**
Operating Voltage: **50 VDC**

Features

Product Type Features

Sealable	No
----------	----

Electrical Characteristics

Dielectric Withstanding Voltage (Max)	500 VAC
Insulation Resistance	100 MΩ
Operating Voltage	50 VDC

Contact Features

Contact Type	Receptacle
Contact Mating Area Plating Material	Gold Flash
Wire Contact Termination Area Plating Material	Tin
Contact Retention Within Housing	Without
Contact Size	1.3mm
Contact Base Material	Copper Nickel Tin
Contact Current Rating (Max)	1 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------



Product Terminates To

Printed Circuit Board

Dimensions

Wire Size	159.8 CMA
-----------	-----------

Usage Conditions

Operating Temperature Range	-25 – 85 °C[-13 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance


For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts




TE Part # 2484140-3
1.0mm P HPI 85deg 2x10 Pos



TE Part # 2484140-6
1.0mm P HPI 85deg 2x25 Pos



TE Part # 2484142-5
1.0mm P HPI - HSG 85deg 2x20 Pos



TE Part # 2484140-1
1.0mm P HPI 85deg 2x6 Pos




TE Part # 2484142-2
1.0mm P HPI - HSG 85deg 2x8 Pos



TE Part # 2484142-4
1.0mm P HPI - HSG 85deg 2x12 Pos




TE Part # 2484142-6
1.0mm P HPI - HSG 85deg 2x25 Pos



TE Part # 2484140-2
1.0mm P HPI 85deg 2x8 Pos




TE Part # 2484142-3
1.0mm P HPI - HSG 85deg 2x10Pos



TE Part # 2484140-5
1.0mm P HPI 85deg 2x20 Pos



TE Part # 2484142-1
1.0mm P HPI - HSG 85deg 2x6 Pos



TE Part # 2484140-4
1.0mm P HPI 85deg 2x12 Pos

Documents

Product Drawings

1.0mm P HPI Terminal, Gold flash Plated

English

CAD Files

Customer View Model

ENG_CVM_CVM_2484144-1_1.3d_igs.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2484144-1_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2484144-1_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



HPI-Connectors-QRG-1221-V2

English

Product Specifications

Application Specification

English