


FEATURES

- **High chemical resistance:** Ensures longevity and reliability in harsh environments
- **Wide temperature range:** Operates effectively from -20 °C to 140 °C
- **Durable material composition:** Made from Fluorinated Ethylene Propylene, Fluoroelastomer, and Viton for enhanced performance
- **Precision dimensions:** Inside diameter of 123.19 mm and outside diameter of 133.85 mm for a perfect fit
- **Compliant with standards:** Meets BS ISO 3601-1, AS 568, EC 1935:2004, and more for quality assurance

RS PRO 123.19 mm O-Ring Seal, Shore A 90 to 95

RS Stock No: 731-406



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO O-Ring Seal is designed for reliable sealing in a variety of industrial applications. Made from high-quality materials including Fluorinated Ethylene Propylene, Fluoroelastomer, and Viton, it offers excellent resistance to chemicals and high temperatures. Ideal for use in environments where durability and performance are critical.

General Specifications

| | |
|--------------|------------------|
| Colour | Black |
| Hardness | Shore A 90 to 95 |
| Product Type | O-Ring Seal |
| Sub Type | O-Ring |

Mechanical Specifications

| | |
|------------------|--|
| Inside Diameter | 123.19 mm |
| Material | Fluorinated Ethylene Propylene, Fluoroelastomer, Viton |
| Outside Diameter | 133.85 mm |
| Thickness | 5.33 mm |

Operation Environment Specifications

| | |
|-------------------------------|--------|
| Maximum Operating Temperature | 140 °C |
| Minimum Operating Temperature | -20 °C |

Approvals

| | |
|---------------------|---|
| Standards/Approvals | BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS |
|---------------------|---|

