



2 YEARS
MANUFACTURER
GUARANTEE



Product number 1173700009
EAN 4007123691975

TECHNICAL DATA

Luminous flux	1000 lm	Battery charging time approx.	3 h
Power consumption	10 W	Number of batteries	1
Colour temperature	6500 K	Battery type	Built-in battery pack
Colour rendering index	80-89 (class 1B)	Battery technology	Lithium-ion
Nominal input voltage	5 V	Impact strength	IK07
Lifetime	33000 h	Protection class	III
Battery capacity	2.2 Ah	Degree of protection (IP)	IP54
Battery voltage	3.7 V	Colour	black/grey
Light duration max.	6 h		

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	0.34 kg
Weight of product (without packaging)	0.24 kg	Dimension LxWxH (incl. packing)	6.5 cm x 12.5 cm x 12 cm
Dimension LxWxH (without packing)	4.5 cm x 10 cm x 10 cm		