


**Part Number :** 734151060

**Product Description :** MCX Jack, Straight, PCB Receptacle, Edge Mount, Brass Body, Gold (Au) Plating, 80 Pieces Per Tray, 50 Ohms

**Series Number :** 73366

**Status :** Active

**Product Category :** RF / Coaxial Connectors



## Documents & Resources

### Drawings

[734151060\\_sd.pdf](#)

### 3D Models and Design Files

[734151060\\_stp.zip](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	ⓘ per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	RF / Coaxial Connectors
Series	73366
Description	MCX Jack, Straight, PCB Receptacle, Edge Mount, Brass Body, Gold (Au) Plating, 80 Pieces Per Tray, 50 Ohms
Product Name	MCX
Style	PCB
Type	Microminiature
UPC	800756039237

### Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

### Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	1.141/g
Orientation	Straight
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Edge Mount
PCB Thickness - Recommended	Various

Reverse Polar	No
Wire/Cable Type	N/A

### Solder Process Data

Max-Duration	10
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	2
Max-Temp	260

---

This document was generated on Jul 09, 2025