



Main

| | |
|---------------------------|--|
| Range | TeSys |
| Product name | TeSys LE |
| Device short name | LE1D |
| Product or component type | Enclosed DOL starter |
| Device application | Standard |
| Utilisation category | AC-3 |
| Device composition | Thermal overload relay ordered separately Contactor |
| Control type | Push-button reset blue R Selector switch 3 positions automatic start/stop/ manual start I-O-II |

Complementary

| | |
|---|--|
| Motor power kW | 4 kW at 380/400 V AC 50/60 Hz 4 kW at 415 V AC 50/60 Hz 4 kW at 440 V AC 50/60 Hz 2.2 kW at 220/230 V AC 50/60 Hz 5.5 kW at 500 V AC 50/60 Hz 5.5 kW at 660/690 V AC 50/60 Hz |
| [Ith] Conventional free air thermal current | 9 A |
| [Uc] control circuit voltage | 230 V AC 50/60 Hz |
| Cable entry number | 2 ISO20 top 2 ISO20 bottom |
| Width | 88 mm |
| Height | 166 mm |
| Depth | 135 mm |
| Net weight | 0.92 kg |

Environment

| | |
|---------------------------------------|------------------------------|
| Material | Polycarbonate |
| IP degree of protection | IP65 conforming to IEC 60529 |
| IK degree of protection | IK07 conforming to IEC 60529 |
| Standards | IEC 60947-4-1 |
| Ambient air temperature for operation | -5...40 °C |
| Environmental characteristic | Standard environment |
| Product certifications | UKCA |

Offer Sustainability

| | |
|----------------------------|--------------------------------|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| Sustainable packaging | Yes |
| RoHS exemption information | Yes |

| | |
|--------------------------|---|
| China RoHS Regulation |  China RoHS Declaration |
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile |  End Of Life Information |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |