


# Black Elastic Rubber Trolley Wheel 125mm, 200kg

Black Elastic Rubber-tyred wheel

PRODUCT

Article number

55-411-125B15



## Product Details

Wheel Rim : lightweight aluminium alloy, reinforced safety design

Tyre : solid, black elastic rubber, bonded to the rim.

Hub : symmetrical, with two precision ball bearings.

## Specifications

Wheel Diameter - ØD ± 1%	<b>125 mm</b>
Hub Type	<b>two ball bearings</b>
Hub Length T1	<b>45 mm ±1</b>
Width of Tread T2	<b>40 mm ±1</b>
Width of Tread-on floor T3	<b>40 mm ±1</b>
Axle Hole Ø d	<b>Ø 15 mm</b>
Hardness of tread A ±4	<b>A 75 Shore</b>
Load capacity	<b>200 Kg</b>
Temperature	<b>-20 / +60 °C</b>
Weight	<b>0,76 Kg</b>

TECHNICAL DATA

## Applications :

Flexible materials handling for heavy loads on uneven surfaces.

Resilient with a low starting effort.

Lightweight wheel, resistant to wear and to side impacts.

Quiet in use. Reduce shock and vibration.

Suitable for trolleys on outdoor or industrial floors (factory, warehouse, truck transport,...).

Towable by mechanized vehicle (max.speed 4Km/h)