

TRIO-PS67/1AC/24DC/3.75/IPD - Power supply unit



1278301

<https://www.phoenixcontact.com/in/products/1278301>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Primary-switched power supply unit TRIO POWER, IPD panel feed-through with Push-in spring connection, Panel mounting, input: 1-phase, output: 24 V DC / 3.75 A

Product description

The robust power supplies with IP67 degree of protection are ideally suited for decentral supply in the field. The weather-resistant cast-aluminum housing protects the devices against dust and water. This enables the power supplies to ensure high system availability even in harsh ambient conditions. The different device connections provide flexibility during mounting.

Your advantages

- Direct installation at the load in the field reduces cable lengths and saves space in the control cabinet
- The robust cast-aluminum housing ensures high system availability with resistance to extreme ambient conditions (temperature, dust, and water)
- High shock and vibration resistance, plus high electric strength
- Improved diagnostic options in the field with DC OK LED and AC OK LED
- NEC Class 2 (POUT <100 W)

Commercial data

Item number	1278301
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CMP
Product key	CMPF13
GTIN	4063151474843
Weight per piece (including packing)	1,016 g
Weight per piece (excluding packing)	766 g
Customs tariff number	85044095
Country of origin	VN

TRIO-PS67/1AC/24DC/3.75/IPD - Power supply unit



1278301

<https://www.phoenixcontact.com/in/products/1278301>

Technical data

Input data

AC operation

Supply system configuration	Star network (TN, TT, IT (PE))
Nominal input voltage range	100 V AC ... 277 V AC
Input voltage range	100 V AC ... 277 V AC -15 % ... +10 % 115 V AC ... 277 V AC ± 10 % (UL)
Derating	< 100 V AC ... 85 V AC (1 %/V)
Switch-on voltage	≥ 80 V AC
Shut-down voltage	< 75 V AC
Typical national grid voltage	120 V AC 230 V AC
Voltage type of supply voltage	AC/DC
Inrush current	≤ 35 A (typical, 277 V AC) 17 A (typical, 120 V AC)
Inrush current integral (I^2t)	< 0.45 A ² s
AC frequency range	50 Hz ... 60 Hz ± 10 %
Frequency range (f_N)	50 Hz ... 60 Hz ± 10 %
Mains buffering time	> 25 ms (120 V AC) > 25 ms (230 V AC)
Current consumption	1 A (100 V AC) 0.4 A (277 V AC)
Protective circuit	Transient surge protection; Varistor
Power factor (cos phi)	> 0.92
Switch-on time	< 0.2 s
Input fuse	4 A (internal (device protection))
Recommended breaker for input protection	6 A ... 16 A (US/CAN: branch circuit protection $\leq 1\frac{1}{2}$ A) (Characteristic B, C, D, K or comparable)
Discharge current to PE	< 0.5 mA

DC operation

Nominal input voltage range	110 V DC ... 250 V DC
Input voltage range	110 V DC ... 250 V DC -20 % ... +10 % 120 V DC ... 250 V DC ± 10 % (UL)
Derating	< 110 V DC ... 88 V DC (1 %/V)
Switch-on voltage	≥ 75 V DC
Shut-down voltage	< 70 V DC
Voltage type of supply voltage	AC/DC
Current consumption	0.88 A (110 V DC) 0.38 A (250 V DC)

Output data

TRIO-PS67/1AC/24DC/3.75/IPD - Power supply unit



1278301

<https://www.phoenixcontact.com/in/products/1278301>

Efficiency	typ. 93 % (120 V AC)
	typ. 94 % (230 V AC)
Nominal output voltage	24 V DC ± 2 %
Nominal output current (I_N)	3.75 A (Class 2 Output)
Derating	> 60 °C ... 70 °C (2.0 %/K)
Feedback voltage resistance	≤ 35 V DC
Protection against overvoltage at the output (OVP)	≤ 35 V DC
Control deviation	< 1 % (change in load, static 10 % ... 90 %)
	< 3 % (Dynamic load change 10 % ... 90 %, 10 Hz)
	< 0.1 % (change in input voltage ± 10 %)
Residual ripple	≤ 10 mV _{PP}
Short-circuit-proof	yes
No-load proof	yes
Output power	90 W
Peak switching voltages nominal load	< 100 mV
Maximum no-load power dissipation	< 0.25 W (120 V AC)
	< 0.28 W (230 V AC)
Power loss nominal load max.	< 7.4 W (120 V AC)
	< 6 W (230 V AC)
Rise time	typ. 100 ms (U_{OUT} (10 % ... 90 %))
Connection in parallel	yes, for increasing power and redundancy with diode
Connection in series	yes, for increased output voltage

Signal: DC OK

Continuous load current	100 mA
-------------------------	--------

Connection data

Input

Connection method	IPD panel feed-through with Push-in spring connection
Conductor cross section, rigid min.	0.5 mm ²
Conductor cross section, rigid max.	2.5 mm ²
Conductor cross section flexible min.	0.5 mm ²
Conductor cross section flexible max.	2.5 mm ²
Single conductor/terminal point, stranded, with ferrule, min.	0.5 mm ²
Single conductor/terminal point, stranded, with ferrule, max.	2.5 mm ²
Conductor cross section AWG max.	14
Color-coded	gray
Type of locking	Clip locking
Number of positions	3

Output

Connection method	IPD panel feed-through with Push-in spring connection
Conductor cross section, rigid min.	0.5 mm ²
Conductor cross section, rigid max.	2.5 mm ²

TRIO-PS67/1AC/24DC/3.75/IPD - Power supply unit



1278301

<https://www.phoenixcontact.com/in/products/1278301>

Conductor cross section flexible min.	0.5 mm ²
Conductor cross section flexible max.	2.5 mm ²
Single conductor/terminal point, stranded, with ferrule, min.	0.5 mm ²
Single conductor/terminal point, stranded, with ferrule, max.	2.5 mm ²
Conductor cross section AWG max.	14
Color-coded	black
Type of locking	Clip locking
Number of positions	3

Signaling

Types of signaling	LED
Status display	2 x LED (green)

Signal output: LED status indicator

Signalization designation	AC OK
Status display	LED
Color	green
AC OK	$AC_{in} > 0.76 \times AC_N$ ($AC_N = 100 \text{ V AC}$)

Signal output: LED status indicator

Signalization designation	DC OK
Status display	LED
Color	green
DC OK	$U_{OUT} > 0.9 \times U_N$ ($U_N = 24 \text{ V DC}$)

Electrical properties

Number of phases	1.00
Insulation voltage input/output	4 kV AC (type test)
	3 kV AC (routine test)

Product properties

Product type	Power supply
Product family	TRIO POWER
MTBF (IEC 61709, SN 29500)	> 1475000 h (25 °C)
	> 1000000 h (40 °C)
	> 500000 h (60 °C)

Insulation characteristics

Protection class	I
Pollution degree	2 (IEC 61010-1)

Dimensions

Item dimensions

Width	100 mm
Height	222 mm

TRIO-PS67/1AC/24DC/3.75/IPD - Power supply unit



1278301

<https://www.phoenixcontact.com/in/products/1278301>

Depth	53 mm
Drill hole	
Diameter	4.2 mm
Installation dimensions	
Installation distance right/left	20 mm / 20 mm
Installation distance top/bottom	50 mm / 100 mm

Mounting

Mounting type	Panel mounting
Assembly note	Alignable: 20 mm horizontally, 20 mm vertically above, 20 mm vertically below
With protective coating	no

Material specifications

Flammability rating according to UL 94 (housing / terminal blocks)	V0
Housing material	Metal
Type of housing	Aluminum (AlMg3)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-25 °C ... 70 °C (Derating > 60 °C: 2 %/K)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Maximum altitude	≤ 4000 m (> 2000 m, Derating: 10 %/1000 m)
Climatic class	4K26 (EN 60721-3-4)
Max. permissible relative humidity (operation)	≤ 100 % (at 25 °C, non-condensing)
Permissible humidity (operation)	≤ 100 % (at 25 °C, non-condensing)
Shock	18 ms, 30g, in each space direction (according to IEC 60068-2-27)
Vibration (operation)	10 Hz ... 59.6 Hz, amplitude ±0.35 mm (in accordance with IEC 60068-2-6)
	59.6 Hz ... 150 Hz, 5g, 20 cycles

Standards and regulations

Overvoltage category

EN 61010-1	II (≤ 4000 m)
------------	---------------

Overvoltage category

EN 62477-1	III (≤ 2000 m)
------------	----------------

Electrical safety

Standard designation	Electrical safety
Standards/specifications	IEC 61010-1 (SELV)

TRIO-PS67/1AC/24DC/3.75/IPD - Power supply unit



1278301

<https://www.phoenixcontact.com/in/products/1278301>

Protective extra-low voltage

Standard designation	Protective extra-low voltage
Standards/specifications	IEC 61010-1 (SELV)
	IEC 61010-2-201 (PELV)

Low-voltage power supplies, DC output

Standard designation	Low-voltage power supplies, DC output
Standards/specifications	EN 61204-3

Safety requirements for electrical equipment for measurement, control, and laboratory use

Standard designation	Safety requirements for electrical equipment for measurement, control, and laboratory use
Standards/specifications	IEC 61010-1

Limit values for harmonic currents

Standard designation	Limit values for harmonic currents
Standards/specifications	EN 61000-3-2

Degrees of protection provided by enclosures (IP code)

Standard designation	Degrees of protection provided by enclosures (IP code)
Standards/specifications	EN/IEC 60529

Mains variation/undervoltage

Standard designation	Mains variation/undervoltage
Standards/specifications	SEMI F47 - 0706

Approvals

UL

Identification	NEC Class 2 according to UL 1310
----------------	----------------------------------

UL

Identification	UL/C-UL Listed UL 61010-1
----------------	---------------------------

UL

Identification	UL/C-UL Listed UL 61010-2-201
----------------	-------------------------------

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Low Voltage Directive	Conformance with Low Voltage Directive 2014/35/EC
Interference emission	Interference emission in accordance with EN 61000-6-3 (residential and commercial) and EN 61000-6-4 (industrial)
Noise immunity	Immunity in accordance with EN 61000-6-1 (residential), EN 61000-6-2 (industrial)

Conducted noise emission

Standards/regulations (Higher requirements in practice (covered))	EN 55016
	EN 61000-6-3 (Class B)
Noise emission	EN 55011 (EN 55022)

TRIO-PS67/1AC/24DC/3.75/IPD - Power supply unit



1278301

<https://www.phoenixcontact.com/in/products/1278301>

Noise emission ()	EN 55016
	EN 61000-6-3 (Class B)
Harmonic currents	
Standards/regulations	EN 61000-3-2
	EN 61000-3-2 (Class A)
Electrostatic discharge	
Standards/regulations	EN 61000-4-2
Electrostatic discharge	
Contact discharge	6 kV (Test Level 3)
Comments	Criterion A
Electromagnetic HF field	
Standards/regulations	EN 61000-4-3
Electromagnetic HF field	
Frequency range	80 MHz ... 1 GHz
Test field strength	10 V/m (Test Level 3)
Frequency range	1 GHz ... 2 GHz
Test field strength	10 V/m (Test Level 3)
Frequency range	2 GHz ... 6 GHz
Test field strength	10 V/m (Test Level 3)
Comments	Criterion A
Fast transients (burst)	
Standards/regulations	EN 61000-4-4
Fast transients (burst)	
Input	4 kV (Test Level 3 - asymmetrical)
Output	2 kV (Test Level 3 - asymmetrical)
Comments	Criterion A
Surge voltage load (surge)	
Standards/regulations	EN 61000-4-5
Surge voltage load (surge)	
Input	1 kV (Test Level 1 - symmetrical)
	2 kV (Test Level 1 - asymmetrical)
Output	0.5 kV (Test Level 1 - symmetrical)
	0.5 kV (Test Level 1 - asymmetrical)
Comments	Criterion B
Conducted interference	
Standards/regulations	EN 61000-4-6
Conducted interference	
Input/Output	asymmetrical

TRIO-PS67/1AC/24DC/3.75/IPD - Power supply unit



1278301

<https://www.phoenixcontact.com/in/products/1278301>

Frequency range	0.15 MHz ... 80 MHz
Comments	Criterion A
Voltage	10 V (Test Level 3)

Voltage dips

Standards/regulations	EN 61000-4-11
Voltage	230 V AC
Frequency	50 Hz
Voltage dip	70 %
Number of periods	25 periods
Comments	Criterion A
Voltage dip	40 %
Number of periods	10 periods
Comments	Criterion B
Voltage dip	0 %
Number of periods	1 period
Comments	Criterion A

Emitted interference


Standards/regulations	EN 61000-6-3
Radio interference voltage in acc. with EN 55011	EN 55011 (EN 55022) Class B, area of application: Industry and residential
Emitted radio interference in acc. with EN 55011	EN 55011 (EN 55022) Class B, area of application: Industry and residential

Criteria

Criterion A	Normal operating behavior within the specified limits.
Criterion B	Temporary impairment to operational behavior that is corrected by the device itself.
Criterion C	Temporary adverse effects on the operating behavior, which the device corrects automatically or which can be restored by actuating the operating elements.


Drawings

Diagram



Power factor

Diagram



Efficiency


TRIO-PS67/1AC/24DC/3.75/IPD - Power supply unit



1278301


<https://www.phoenixcontact.com/in/products/1278301>

Dimensional drawing




Device dimensions (dimensions in mm)

Diagram



Input current/output current

Diagram




Output current/installation altitude

TRIO-PS67/1AC/24DC/3.75/IPD - Power supply unit



1278301

<https://www.phoenixcontact.com/in/products/1278301>



Block diagram

TRIO-PS67/1AC/24DC/3.75/IPD - Power supply unit



1278301

<https://www.phoenixcontact.com/in/products/1278301>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1278301>



cULus Listed

Approval ID: FILE E 123528



cULus Listed

Approval ID: FILE E 123528

TRIO-PS67/1AC/24DC/3.75/IPD - Power supply unit



1278301

<https://www.phoenixcontact.com/in/products/1278301>

Classifications

ECLASS

ECLASS-11.0	27040701
ECLASS-12.0	27040701
ECLASS-13.0	27040701

ETIM

ETIM 9.0	EC002540
----------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	56686b9f-d5ad-44b1-8aa4-d4c784092108

TRIO-PS67/1AC/24DC/3.75/IPD - Power supply unit



1278301

<https://www.phoenixcontact.com/in/products/1278301>

Accessories

STEP3-DIODE/5-24DC/2X5/1X10/PT - Redundancy module

1283937

<https://www.phoenixcontact.com/in/products/1283937>



Redundancy module STEP DIODE, DIN rail mounting, 5 V DC ... 24 V DC, 1x 10 A, 2x 5 A

IPD WD 3P2,5 M20 GY - Panel feed-through

1047319

<https://www.phoenixcontact.com/in/products/1047319>



Panel feed-through, Direct connection, product family: IPD, connection method: Push-in connection/ Push-in connection, number of positions: 2+PE, M20, 0.5 mm² ... 2.5 mm², 600 V, 20 A, PA, light gray, external cable diameter: 6 mm ... 9 mm and 8 mm ... 13 mm

TRIO-PS67/1AC/24DC/3.75/IPD - Power supply unit



1278301

<https://www.phoenixcontact.com/in/products/1278301>

IPD WD 3X2,5 M20 BK - Panel feed-through

1189585

<https://www.phoenixcontact.com/in/products/1189585>



Panel feed-through, Direct connection, product family: IPD, connection method: Push-in connection/ Push-in connection, M20, 0.5 mm² ... 2.5 mm², 600 V, 15 A, PA, black, external cable diameter: 6 mm ... 9 mm and 8 mm ... 13 mm

IPD SEAL W26 1XASI - Seal

1698175

<https://www.phoenixcontact.com/in/products/1698175>



Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in