



## Main

Range of product	New Unica
Product or component type	Key switch
Device presentation	Mechanism
Technology type	Electromechanical
Switch function	3 positions
Device application	Light control
Provided equipment	Keys
Colour tint	Anthracite (RAL 7021)
Type of packing	Flow-pack

## Complementary





Rated current	16 A
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Electrical durability	20000 cycles, cos phi = 0.6
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening distance	> 3 mm
Actuator	Key
Number of modules	2 modules
Connections - terminals	Screw terminals
Cable cross section	0...2.5 Mm² rigid cable 0...2.5 mm² flexible cable
Material	Thermoplastic ABS-UV stabilised: mechanism rocker
Marking	Without marking
Surface finish	Matt
Specific treatment - integrated within the material	Painted
Fixing mode	Clip-in
Width	45 mm
Height	45 mm
Depth	74 mm
Embedding depth	31 mm
Net weight	0.0505 kg
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-5...50 °C
Standards	LV directive IEC 60669-1

Product certifications	CE
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

## Environment

IP degree of protection	IP4X
IK degree of protection	IK04
Environmental characteristic	Oil UV resistant Acetone Liquid soap Window-cleaning fluid Petrol Alcohol Bleach

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins