PSMR25-9-7-SS

Ruland PSMR25-9-7-SS, 9mm x 7mm Four Beam Coupling, Stainless Steel, Set Screw Style, 25.4mm OD, 31.8mm Length



Description

Ruland PSMR25-9-7-SS is a set screw style four beam coupling with 9mm x 7mm bores, 25.4mm OD, and 31.8mm length. It is machined from a single piece of material and feature two sets of two spiral cuts. This gives it higher torque capacity, lower windup, and larger body sizes than single beam couplings. PSMR25-9-7-SS is zero-backlash and has a balanced design for reduced vibration at high speeds of up to 6,000 RPM. This four beam spiral coupling is zero-backlash and has a balanced design for reduced vibration at high speeds of up to 6,000 RPM. All hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. PSMR25-9-7-SS is made from 303 stainless steel for increased torque capacity. It is machined from bar stock that is sourced exclusively from North American mills and RoHS3 and REACH compliant. PSMR25-9-7-SS is manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

Product Specifications

Bore (B1)	9 mm	**Small Bore (B2)**	7 mm
B1 Max Shaft Penetration	14.7 mm	**B2 Max Shaft Penetration**	14.7 mm
Outer Diameter (OD)	1.000 in (25.4 mm)	**Bore Tolerance**	+0.025 mm / -0.000 mm
Length (L)	1.250 in (31.8 mm)	**Recommended Shaft Tolerance**	+0.000 mm / -0.013 mm
Forged Set Screw	M4	**Screw Material**	Alloy Steel
Hex Wrench Size	2.0 mm	**Screw Finish**	Black Oxide
Seating Torque	1.76 Nm	**Number of Screws**	4 ea
Dynamic Torque Reversing	1.16 Nm	**Angular Misalignment**	3.0°
Dynamic Torque Non-Reversing	2.32 Nm	**Parallel Misalignment**	0.38 mm
Static Torque	4.63 Nm	**Axial Motion**	0.25 mm
Torsional Stiffness	0.91 Deg/Nm	**Moment of Inertia**	9.275 x10^{-6} kg-m^2
Maximum Speed	6,000 RPM	**Full Bearing Support Required?**	Yes
Zero-Backlash?	Yes	**Torque Wrench**	TW:BT-1R-1/4-15.6
Recommended Hex Key	Metric Hex Keys	**Material Specification**	Type 303 Austenitic, Non-Magnetic Bar
Temperature	-40°F to 350°F (-40°C to 176°C)	**Finish Specification**	Bright, No Plating
Manufacturer	Ruland Manufacturing	**Country of Origin**	USA
Weight (lbs)	0.226000	**UPC**	634529050422
Tariff Code	8483.60.8000	**UNSPC**	31163003
Note 1	Torque ratings are at maximum misalignment.		
Note 2	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Note 3	Torque ratings for the couplings are based on the physical limitations/failure point of the machined beams. Under normal/typical conditions the hubs are capable of holding up to the rated torque of the machined beams. In some cases, especially when the smallest standard bores are used or where shafts are undersized, slippage on the shaft is possible below the rated torque of the machined beams. Please consult technical support for more assistance.		
Prop 65	**WARNING** This product can expose you to chemicals including Ethylene Thiourea and Nickel (metallic), known to the State of California to cause cancer		

Installation Instructions

1. Align the bores of the PSMR25-9-7-SS four beam coupling on the shafts that are to be joined and determine if the misalignment parameters are within the limits of the coupling. (*Angular Misialignment:* 3Â°, *Parallel Misalignment*: 0.38 mm, *Axial Motion*: 0.25 mm)
2. Fully tighten the M4 screws on one hub to the recommended seating torque of 1.76 Nm using a 2.0 mm hex torque wrench.
3. Before tightening the screws on the second hub, rotate the coupling by hand to allow it to reach its free length.
4. Tighten the screws on the second hub to the recommended seating torque. Make sure the coupling remains axially relaxed and the misalignment angle remains centered along the length of the coupling.
5. The shafts may extend into the relieved portion of the bore as long as it does not exceed the shaft penetration length of 14.7 mm.