



Diffuse reflection sensor

OUT-DPKG



receiver in upper lens
transmitter in lower lens



Product characteristics

Type of light	infrared light
Housing	rectangular

Application

Function principle	Diffuse reflection sensor
--------------------	---------------------------

Electrical data

Operating voltage	[V]	10...55 DC
Current consumption	[mA]	35; ((24 V))
Protection class		II
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	880

Outputs

Electrical design		PNP
Output function		dark-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	160
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Range	[mm]	1...200; (white paper 200 x 200 mm)
Range adjustable		yes
Max. light spot diameter	[mm]	180
Light spot dimensions refer to		at maximum range

Operating conditions

Ambient temperature	[°C]	-25...80
---------------------	------	----------



Diffuse reflection sensor

OUT-DPKG

Protection	IP 67
------------	-------

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[years]	685

Mechanical data

Weight	[g]	152
Housing		rectangular
Dimensions	[mm]	28 x 16 x 51
Materials		PPO modified
Lens material		glass
Lens alignment		side lens

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied	Angle bracket: 1, E20211
----------------	--------------------------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 2 m, PVC; 3 x 0.34 mm²

Connection



BN	brown
BU	blue
BK	black



Diffuse reflection sensor

OUT-DPKG

Diagrams and graphs

excess gain graph

