


FEATURES

- **High Chemical Resistance:** Suitable for use with a wide range of chemicals, enhancing versatility.
- **Temperature Range:** Operates effectively between -20 °C and 140 °C, allowing for use in various environments.
- **Durable Material:** Constructed from Fluorinated Ethylene Propylene and Viton, providing long-lasting performance.
- **Standard Compliance:** Meets BS ISO 3601-1, AS 568, and other key standards, ensuring quality and reliability.
- **Shore A Hardness 90 to 95:** Offers a balance of flexibility and strength for effective sealing.

RS PRO 104.37 mm O-Ring Seal, Fluorinated Ethylene Propylene

RS Stock No: 731-371



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO O-Ring Seal is designed for reliable sealing in a variety of industrial applications. Made from high-quality materials such as Fluorinated Ethylene Propylene and Viton, it offers excellent chemical resistance and durability. Ideal for use in environments with temperatures ranging from -20 °C to 140 °C, this O-Ring ensures optimal performance and longevity.

General Specifications

Colour	Black
Hardness	Shore A 90 to 95
Product Type	O-Ring Seal
Sub Type	O-Ring

Mechanical Specifications

Inside Diameter	104.37 mm
Material	Fluorinated Ethylene Propylene, Fluoroelastomer, Viton
Outside Diameter	111.43 mm
Thickness	3.53 mm

Operation Environment Specifications

Maximum Operating Temperature	140 °C
Minimum Operating Temperature	-20 °C

Approvals

Standards/Approvals	BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS
---------------------	---

