



Specification SPL82 Data Logger Sound Level Meter



Measuring level range: 30 – 130dB
Resolution: 0.1dB
Frequency range: 20Hz – 8kHz
Frequency weighting: A or C
Level ranges: Lo: 30 – 90dB
Med: 50 – 110dB
Hi: 70 – 130dB
Accuracy: ± 1.4 dB (under reference conditions
@ 94dB, 1KHz)
Dynamic range: 60dB
Time weighting: fast or slow
Microphone: ½ inch electret condenser microphone
AC output: 1Vrms at full scale (full scale is the upper
limit of the
selected level range)
DC output: 10mV/dB

GENERAL

Digital display: 4 digit liquid crystal display
Sampling rate: twice per second

Analogue display: 30 segment bar graph
Analogue resolution: 2dB
Analogue measurement rate: 20 times per second
Alarm function:

OVER is when output is more than the upper limit of the range
(over 130dB).

UNDER is when output is less than the lower limit of the range
(under 30dB).



Specification SPL82 Data Logger Sound Level Meter

Data logging capacity: 64,000 records
Power: 4 x 1.5V AAA alkaline batteries (IEC LR03, NEDA 24A)
Battery life: 24 hours (approximate)
Auto power off: 30 mins (can be disabled)
Power consumption: 0.2W approx
External power supply: 5V DC (micro USB plug)
Dimensions: 264 (L) x 63 (W) x 29mm (H)
Weight: 245g including battery
Includes: storage case, 4 x 1.5V AAA alkaline batteries, software,
micro USB cable, 3.5mm plug, USB stick and instruction
manual.

ENVIRONMENTAL

Operating conditions: Temperature: 0°C to 40°C (32 to 104°F)
Relative humidity: 10 to 90% R.H.
Storage conditions: Temperature: -10°C to 60°C (14 to 140°F)
Relative humidity: 10 to 75% R.H.

FUNCTIONALITY

Complies with BS EN 61672-1 Class 2

EMC

Conforms to BS EN 61326-1

Check out what else you can get from Martindale:

- 18th Edition Testers
- Accessories
- Calibration Equipment
- Continuity Testers
- Electricians' Kits
- Environmental Products
- Full Calibration & Repair Service
- Fuse Finders
- Digital Clamp Meters
- Digital Multimeters
- Labels
- Microwave Leakage Detectors
- Motor Maintenance Equipment
- Multifunction Testers
- Non-trip Loop Testers
- Pat Testers & Accessories
- Phase Rotation Testers
- Proving Units
- Socket Testers
- Thermometers & Probes
- Test Leads
- Voltage Indicators
- Specialist Metrohm Testers (4 & 5kV)
- Specialist Drummond Testers



Martindale Electric Company Limited
Tel: +44(0)1923 441717 Fax: +44 (0)1923 446900
E-mail: sales@martindale-electric.co.uk
Website: www.martindale-electric.co.uk

© Martindale Electric Company Ltd. 2018
Registered in England No. 3387451. Rev 2 LIT82

