

OSE 2-80 EC Set

Compact orbital sander with speed control

Order no. 468924

GTIN 4030293209787



- + Lightweight, compact one-handed orbital sander, very ergonomic and low-vibration thanks to special balancing for fatigue-free and joint-friendly work
- + Ergonomically designed, handy grip cover with soft grip insert ensures a secure grip and good guidance
- + Brushless motor with greater efficiency and a longer service life
- + Electronics: Speed preselection with 4 settings, constant speed control by means of tachogenerator, soft start, restart protection
- + Sanding speed suitable for the material thanks to electronic speed adjustment
- + Hook & loop backing pad with 12-hole system for optimum extraction, suitable for all standard abrasives
- + E-signal switch for simple, safe operation with quick-stop function prevents trailing of the backing pad
- + Equipped with disc brake, as a result no unwanted sanding marks are produced on the workpiece and expensive corrective finishing is not required
- + Effective dust extraction thanks to integrated extractor for dust-free working with filter cartridge
- + External dust extraction Ø 27 mm, antistatic suction hose SH 27x3,5m AS (445.045) can be connected
- + Impact-resistant filter cartridge with exchangeable PES filter allows simple dust disposal or cleaning of the filter as well as maximum service life
- + Especially suitable for overhead work



Technical data

Power consumption	260 W
Voltage	230 V
Frequency	50/60 Hz
Stroke	2.0 mm
Backing pad length	130 mm
Backing pad width	80 mm
Orbit rate, no load	16000 - 24000 rpm
No-load speed	8000 - 12000 rpm
Diameter dust extraction connection	Ø 27
Cable length	4.0 m
Dimensions WxLxH	163 x 90 x 121 mm
Weight	1.2 kg

Standard equipment

- 1 Hook-and-loop backing pad (469009)
- 1 PES microfilter cartridge (486833)
- 1 Carrying case L-BOXX® (414085)
- 1 Case insert (516066)