

313.3240**CONNECTOR****32A 2P+E 4h 100-130V 50Hz 60Hz****Screw terminals**

* Product image may be indicative



EN IEC 60309-1 (2022)

EN IEC 60309-2 (2022)

Low voltage direct. 2014/35/EU

■ GENERAL CHARACTERISTICS

Commercial Series OPTIMA Series

Synthetical description CONNECTOR

Description

The connector of the OPTIMA Series is engineered for a rated voltage of 100-130V and a rated current of 32A. Featuring a 2P+E configuration and a 4h hour position, it operates efficiently at both 50Hz and 60Hz frequencies. With a protection degree of IP44/IP54, it ensures robust performance in various environments. Equipped with screw terminals and straight type outlets, it offers reliable connectivity.

Mounting version PORTABLE

■ TECHNICAL CHARACTERISTICS

Rated current 32A

Poles 2P+E

Hour position 4h

Rated voltage 100-130V

Working frequency 50Hz

60Hz

Terminals Screw terminals

■ PHYSICAL CHARACTERISTICS

Mounting version PORTABLE

Colour YELLOW

Material THERMOPLASTIC

Protection degree Splash proof

Protection degree IP IP44/IP54

Protection degree IK IK08

Types of available outlets STRAIGHT

Contact material CuZn (brass)

Cable entry CABLE GLAND

■ DOWNLOAD

Technical drawing [PDF]

Technical drawing [STP]

Technical drawing [DWG]