

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0152660073**
Status: **Active**
Overview: Premo-Flex™ Cable Jumpers
Description: 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 8 Circuits, 0.03m Cable Length, 0.27mm Cable Thickness, Tin (Sn) Plating

Documents:

| | |
|--|--|
| Drawing (PDF) | Packaging Specification PK-15266-001-001 (PDF) |
| Product Specification PS-15266-001-001 (PDF) | RoHS Certificate of Compliance (PDF) |

General

| | |
|-------------------------|-----------------------------------|
| Product Family | Cable |
| Series | 15266 |
| Comments | Contacts on the same side, Type A |
| Crimp Quality Equipment | Yes |
| Overview | Premo-Flex™ Cable Jumpers |
| Product Name | Premo-Flex™ FFC Jumper |
| UPC | 884982428362 |

Physical

| | |
|-------------------------------|-----------------|
| Cable Length | 0.03m |
| Circuits (Loaded) | 8 |
| Circuits (maximum) | 8 |
| Net Weight | 0.091/g |
| Packaging Type | Bag |
| Pitch - Termination Interface | 0.50mm |
| Temperature Range - Operating | -40°C to +105°C |
| Wire Size AWG | N/A |
| Wire/Cable Type | Flat Flex Cable |

Electrical

| | |
|-------------------------------|--------|
| Current - Maximum per Contact | 0.5A |
| Voltage - Maximum | 60V AC |

Material Info

Reference - Drawing Numbers

| | |
|-------------------------|------------------|
| Packaging Specification | PK-15266-001-001 |
| Product Specification | PS-15266-001-001 |
| Sales Drawing | SD-15266-001 |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

| | |
|-----------------|--------------|
| China ROHS | Not Reviewed |
| ELV | Not Relevant |
| RoHS Phthalates | Not Reviewed |

Search Parts in this Series

15266 Series

Use With

Molex FFC – FPC connector. Be sure to match like plating.