



### Main

Range	Acti9
Product name	Acti9 Isobar B
Product or component type	Loose enclosure
Device application	Distribution
Provided equipment	1 DIN rail Door Slotted front cover enclosure

### Complementary

Enclosure mounting	Surface
Number of ways	85 (1P)
Number of horizontal rows	5
Enclosure material	Folded sheet steel: RAL 9001 epoxy powder coat
Height	1024 Mm
Depth	138 Mm
Width	470 Mm

### Environment

IP degree of protection	IP3x conforming to BS EN 60529
-------------------------	--------------------------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18.0 Cm
Package 1 Width	48.0 Cm
Package 1 Length	102.0 Cm
Package 1 Weight	21.3 Kg
Unit Type of Package 2	PAM
Number of Units in Package 2	12
Package 2 Height	112.0 Cm
Package 2 Width	100.0 Cm
Package 2 Length	120.0 Cm
Package 2 Weight	270.6 Kg

### Environmental data

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	245

### Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : <b>Commercialised</b>
---