



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKD
Head type	Plunger head
Product compatibility	XCKS
Associated body	ZCKS2H29 ZCKS8H29 ZCKS8 ZCKS5H29 ZCKS2 ZCKSD39 ZCKS5 ZCKSD31 ZCKSD35H29 ZCKS6 ZCKS9 ZCKS7H29 ZCKS9H29 ZCKSD37H29 ZCKS6H29 ZCKSD31H29 ZCKS7 ZCKSD35 ZCKS1 ZCKSD37 ZCKSD39H29 ZCKS1H29
Movement of operating head	Linear
Type of operator	End plunger spring return metal
Type of approach	Vertical approach, 1 direction

Complementary

Switch actuation	On end
Positive opening	With

Head material	Plastic
---------------	---------

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------