

Swivel Stem Castor, grey rubber 80mm, 50kg

Swivel Stem Castor

PRODUCT

Article number

DP2FA080-325L12

DP2FD080-325L12



Product Details

Castor assembly : Pressed steel, zinc plated housing, with threaded stem fitting.

Swivel : Swivel on two rows of balls

Double-acting lock on wheel and pivot. Grey nylon pedal.

Rim : Grey Polypropylene.

Tread : Grey synthetic Rubber. Non-marking.

Specifications	Threaded Stem	
Wheel Diameter - ØD ± 1%	80 mm	
Hub Type	Plain bore	
Hub Length	24 mm ±1	
Width of Tread	22mm ±1	
Width of Tread-on floor	22 mm ±1	
Overall Height	109 mm	
Offset	25 mm	
Fitted Stem Diameter	12 mm	
Fitted stem Height	25 mm	
Hardness of tread A ±3	A 80° Shore	
Load capacity	50 Kg	
Temperature	-5 / +50 °C	
Weight	Swivel = 0,37 kg	Swivel+brake = 0,42 kg

TECHNICAL DATA

Applications :

Medium-weight appliances and furniture.

Non-marking. Materials handling on indoor or warehouse floors.

Quiet.

Easy to assemble with the crimped stem.

Stem is united to the housing.