



Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies > M12 A-Code Pigtail, Male, R/A



Cable Assembly Type: **M12 Pigtail**

Number of Positions: **4**

Cable Assembly Length: **5 m**

M8/M12 Application Type: **Sensor/Actuator**

Connector & Keying Code: **A**

[All M12 A-Code Pigtail, Male, R/A \(0\)](#)

Features

Product Type Features

|                        |             |
|------------------------|-------------|
| Cable Assembly Type    | M12 Pigtail |
| Cable Assembly (End A) | M12 Plug    |

Configuration Features

|                      |   |
|----------------------|---|
| Configuration Number | A |
| Number of Positions  | 4 |

Electrical Characteristics

|                   |        |
|-------------------|--------|
| Operating Voltage | 60 VDC |
|-------------------|--------|

Body Features

|                         |                           |
|-------------------------|---------------------------|
| Jacket Material         | PUR                       |
| Connector Color (End A) | Blue                      |
| Cable Color             | Gray                      |
| Wire Color (Base)       | Brown, White, Blue, Black |
| Connector & Keying Code | A                         |

Contact Features

|                              |     |
|------------------------------|-----|
| Contact Current Rating (Max) | 4 A |
|------------------------------|-----|

Mechanical Attachment

|             |     |
|-------------|-----|
| Thread Size | M12 |
|-------------|-----|



|                               |                 |
|-------------------------------|-----------------|
| Connector Orientation (End A) | Right Angle     |
| Housing Features              |                 |
| Housing Material              | Plastic         |
| Dimensions                    |                 |
| Outside Cable Diameter        | 5.9 mm[.23 in]  |
| Wire Size                     | 22 AWG          |
| Operation/Application         |                 |
| M8/M12 Application Type       | Sensor/Actuator |
| Shielded                      | Yes             |
| Packaging Features            |                 |
| Packaging Method              | Box             |
| Packaging Quantity            | 25              |
| Other                         |                 |
| Field Serviceable             | Yes             |
| Cable Assembly Length         | 5 m             |
| Cable Assembly Configuration  | Single Ended    |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Compliant   |
| EU ELV Directive 2000/53/EC                   | Compliant   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2022 (223)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free   |
| Solder Process Capability                     | Not applicable for solder process capability  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Customers Also Bought



TE Part #0146666001  
DSPL-NR3-0-65MM

## Documents

- Datasheets & Catalog Pages
- M8 / M12 Connector System Catalog
- English
- M8 / M12 Connector System Catalog
- Japanese

- Product Specifications
- Product Specification
- English