

**194S0012**

**Flexible current sensors ROGOWSKI RGW-120 loop Ø: 40/loop length: 126**

**Strong points**

- Excellent accuracy
- Secure locking
- Installation

**General characteristics**

- Used with DIRIS A-30, A-41, A-60, Q800, COUNTIS P44-RGW and ATyS C65.

**Compliance with standards**

- IEC 60529
- IEC 61869-10
- UKCA

**Link to the reference**



<https://emea.socomec.com/en/reference/194S0012>

RGW\* flexible current sensors measure load currents and are particularly suitable for existing installations. RGW sensors have an extended measuring range of up to 5000 A as well as 6 aperture diameters to have the most suitable measurement solution for your needs. The measurement signal can be transmitted to meters and PMDs with 1 A input(s).

\*only compatible with the addition of the RAC-1A integrator.

**Classification**

UNSPSC	41113637
ETIM Class	EC002048
IGCC	5343

**Commerce**

Description	Flexible current sensors ROGOWSKI 120mm for integrator RAC-1A class 0.5, 100-5000 current range, these RGW measure load currents and are especially suitable for existing installations
Effective date	2023-05-31
Offer Life Cycle Code	40
Country of origin	IT

**Logistics**

GTIN/EAN	3596033231063
Customs number	8504312990
Price unit	PC
Weight of the packing unit [kg]	0.142
Length of the packing unit [m]	0.01
Width of the packing unit [m]	0.18
Depth of the packing unit [m]	0.16

**Technical Characteristics**

Function	Current measurement
Type of current	AC
Type of product	Flexible
Internal diameter	120
Secondary Output	Voltage
Accuracy class	0.5
Type of connection	Cable
Conformity to standards	IEC 61869-2
Customisable	No