

# VS-09-ST-DSUB-CD-G - D-SUB contact support



1688832

<https://www.phoenixcontact.com/gb/products/1688832>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB contact carrier, Shell size 1, for 9 signal contacts, pin contact type, for crimp contacts, straight, attachment with M3 thread, for VS-09-... panel mounting frames



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1688832       |
| Packing unit                         | 100 pc        |
| Minimum order quantity               | 100 pc        |
| Sales key                            | ABNCAA        |
| Product key                          | ABNCAA        |
| GTIN                                 | 4017918822965 |
| Weight per piece (including packing) | 6.41 g        |
| Weight per piece (excluding packing) | 10.63 g       |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# VS-09-ST-DSUB-CD-G - D-SUB contact support



1688832

<https://www.phoenixcontact.com/gb/products/1688832>

## Technical data

### Product properties

|                     |                |
|---------------------|----------------|
| Product type        | Contact insert |
| Type                | D-SUB          |
| Number of positions | 9              |
| Connection profile  | D-SUB 9        |
| Shielded            | no             |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 2   |

### Electrical properties

|                                            |                |
|--------------------------------------------|----------------|
| Rated voltage in acc. with IEC 61076-2-101 | 400 V          |
| Rated voltage (III/3)                      | 125 V          |
| Rated current                              | 5 A (at 20 °C) |
| Test voltage                               | 1200 V         |
| Transmission medium                        | Copper         |

### Connection data

|                   |                  |
|-------------------|------------------|
| Connection method | Crimp connection |
|-------------------|------------------|

### Dimensions

|        |          |
|--------|----------|
| Width  | 18 mm    |
| Height | 12.93 mm |
| Length | 31.19 mm |

### Material specifications

|                                        |                                                 |
|----------------------------------------|-------------------------------------------------|
| Flammability rating according to UL 94 | V0                                              |
| Housing material                       | Steel, tin-plated                               |
| Contact material                       | Copper alloy                                    |
| Contact carrier material               | Glass-fiber reinforced thermoplastics, UL 94 V0 |

### Mechanical properties

#### Mechanical data

|                                    |          |
|------------------------------------|----------|
| Insertion/withdrawal cycles        | ≥ 500    |
| Insertion force per signal contact | ≤ 3.40 N |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -55 °C ... 130 °C |
|---------------------------------|-------------------|

# VS-09-ST-DSUB-CD-G - D-SUB contact support



1688832

<https://www.phoenixcontact.com/gb/products/1688832>

| Mounting type | Threads |
|---------------|---------|
|---------------|---------|

# VS-09-ST-DSUB-CD-G - D-SUB contact support



1688832

<https://www.phoenixcontact.com/gb/products/1688832>

## Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1688832>



**UL Recognized**

Approval ID: E118976

# VS-09-ST-DSUB-CD-G - D-SUB contact support



1688832

<https://www.phoenixcontact.com/gb/products/1688832>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440302 |
| ECLASS-15.0 | 27440323 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001132 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# VS-09-ST-DSUB-CD-G - D-SUB contact support



1688832

<https://www.phoenixcontact.com/gb/products/1688832>

## Environmental product compliance

### EU RoHS

|                                         |              |
|-----------------------------------------|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 6(a), 6(a)-I |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | e44cdf9a-994f-46f5-a530-5697c4adb337 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)