

HDP24-24-19SE

✓ ACTIVE

DEUTSCH | DEUTSCH HD, DEUTSCH HDP

TE Internal #: HDP24-24-19SE

Hybrid, Housing for Female Terminals, Wire-to-Wire, 19 Position,
Sealable, Black, Wire & Cable, Power & Signal

[View on TE.com >](#)



Connectors > Automotive Connectors > Connector Housings > DEUTSCH HDP20 HOUSINGS



Connector & Housing Type: **Housing for Female Terminals**

Mating Pin Diameter: **1.59 mm, 2.39 mm [.063 in, .094 in]**

Connector System: **Wire-to-Wire**

Number of Positions: **19**

Sealable: **Yes**

[All DEUTSCH HDP20 HOUSINGS \(326\)](#)

Features

Product Type Features

Connector & Housing Shape	Circular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	Yes
Hybrid Connector	Yes
Primary Locking Feature	Contact Retainer
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Blank Cavity Position	0
Connector Seal Code	E Seal
Number of Positions	19

Electrical Characteristics

Operating Voltage	250 VAC
Nominal Voltage Architecture	12 V, 24 V, 48 V

Body Features

Cable Exit Angle	180°
Body Material	PA GF



Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Size	Size 12, Size 16
Mating Pin Diameter	1.59 mm, 2.39 mm[.063 in][.094 in]
Contact Current Rating (Max)	13 A, 25 A

Mechanical Attachment

Mounting Feature	With
Terminal Position Assurance	No
Strain Relief	Add By Accessory
Mating Alignment Type	Not Keyed
Mating Alignment	Without
Connector Mounting Type	Cable Mount (Free-Hanging), Panel Mount

Dimensions

Product Width	50.8 mm[2 in]
Product Length	41.86 mm[1.648 in]
Product Height	47.63 mm[1.875 in]
Accepts Wire Insulation Diameter Range	1.35 – 3.05 mm, 2.46 – 4.01 mm[.053 – .12 in][.097 – .158 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Degree of Protection	IP67
UL Flammability Rating	20mm Flame Test per Standard UL-94

Packaging Features

Packaging Method	Box
------------------	-----

Other

Serviceable	Yes
Connector Position Assurance Capable	No



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-D48-ST273
DEUTSCH SOLID CONTACTS



TE Part # CAT-H396-CH8172
DEUTSCH HDP20 HOUSINGS



TE Part # CAT-D48-SP729
DEUTSCH SEALING PLUGS



TE Part # CAT-D48-SFT273
DEUTSCH STAMPED & FORMED CONTACTS



TE Part # CAT-H396-RC8382
DEUTSCH HDP20 RECEPTACLE
PROTECTIVE CAPS

TE Part # 24-D-PUNCH
D-HOLE PUNCH, SIZE 24

TE Part # 0411-337-1205
EXT TOOL, SIZE 12, 12-14 AWG, E,
ORG

TE Part # HD30-24BT-BK
BOOT, 24SZ, ST, BLK

TE Part # HD30-24BT
BOOT, 24SZ, ST, GRY

TE Part # HD30-24BT-90-BK
BOOT, 24SZ, RA, BLK

TE Part # CAT-H3930-B128
DEUTSCH HD30 BACKSHELLS

TE Part # 0411-336-1605
EXT TOOL, SIZE 16, 16-20 AWG, E,
DRK BLU

TE Part # 16-04477
GASKET, 24SZ, BLK, HD30

TE Part # 62036-40
62036 HDP24 FLANGE-SEAL silicone
60shore

TE Part # MT-90BT-HT-24
BOOT, 24SZ, RA, HI TEMP, YEL

TE Part # MT-90BT-HT-24BK
BOOT, 24SZ, RA, HI TEMP, BLK

Also in the Series | **DEUTSCH HD**

Automotive Connector Caps & Covers
(59)

Automotive Housings(744)

Automotive Seals & Cavity Plugs(10)

Insertion & Extraction Tools(11)

Other Automotive Connector
Accessories(11)

Also in the Series | **DEUTSCH HDP**



Automotive Connector Caps & Covers (12)



Automotive Housings(333)



Insertion & Extraction Tools(11)



Other Automotive Connector Accessories(5)

Customers Also Bought



TE Part #DT04-08PA-CL06
REC, 8P, BLK, E, FLANGE, A




TE Part #HC5730
LEAD CONNECTOR 25MM +VE



TE Part #HC5731
LEAD CONN. 25mm -VE



TE Part #HC5733
35MM2 NEG LEAD CONNECTOR 1/4" UNC THREAD



TE Part #HC5738
95MM2 POSBAT LEAD 1/4" UNC THREAD



TE Part #HC5739
95MM2 NEGBAT LEAD 1/4" UNC THREAD



TE Part #HC5840D
INTEGRAL BATT. POST. DOUBLE TAPER.



TE Part #HC5841
70MM2 BATTTERY CLMP ASSMB NEGATIVE



TE Part #HC5936
BATTERY LEAD CONN. 70mm +VE



TE Part #HC5955
BATT.LEAD. 90DEG.70MM+JC

Documents

Product Drawings

REC, 19P, BLK, E, 12/16, S

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_HDP24-24-19SE_B.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_HDP24-24-19SE_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_HDP24-24-19SE_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ICT Terminals and Connectors Catalogue](#)

English

[CONNECTOR SELECTOR](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English