



MICTOR

TE Internal #: 2-5767004-5

PCB Mount Receptacle, Vertical, Board-to-Board, 152 Position, .64 mm [.025 in] Centerline, Fully Shrouded, Gold (Au), Surface Mount, Signal, Black

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **152**

Centerline (Pitch): **.64 mm [.025 in]**

Features

Product Type Features

Ground Feature Type	Ground Bus
PCB Connector Type	PCB Mount Receptacle
Connector System	Board-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Columns	76
Number of Signal Positions	152
Number of Power Positions	4
Board-to-Board Configuration	Parallel
Stackable	No
PCB Mount Orientation	Vertical



Number of Positions	152
---------------------	-----

Electrical Characteristics

Operating Voltage	4 VDC
Impedance	50 Ω
Insulation Resistance	2 MΩ
Dielectric Withstanding Voltage (Max)	500 VAC

Signal Characteristics

Data Rate	10 Gb/s
Differential Signaling	Yes

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

PCB Contact Termination Area Plating Material Finish	Matte
Contact Mating Area Plating Material Thickness	.76 μm[29.92 μin]
PCB Contact Termination Area Plating Material Thickness	3.81 μm[149.9997 μin]
Contact Shape & Form	Dual Beam
Contact Layout	Inline
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Finish	Matte
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Socket
Contact Current Rating (Max)	11.5 A

Termination Features

Rectangular Termination Post & Tail Width	.54 mm[.021 in]
Rectangular Termination Post & Tail Thickness	.2 mm[.008 in]
Termination Method to PCB	Surface Mount

Mechanical Attachment

Mating Retention	With
PCB Mount Retention Type	Boardlock
PCB Mount Alignment Type	Positioning Bosses
PCB Mount Retention	With



PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	Without

Housing Features

Mating Entry Location	Top
Housing Material	Matte
Centerline (Pitch)	.64 mm [.025 in]

Dimensions

Stack Height	2.5 mm, 6.6 mm, 9 mm, 10.92 mm, 17.96 mm, 18.75 mm, 20 mm, 22.86 mm [.9 in]
Connector Width	6.9 mm [.272 in]
PCB Thickness (Recommended)	1.57 mm [.8 in]
Connector Height	5.99 mm [.236 in]
Connector Length	63.45 mm [2.498 in]

Usage Conditions

Operating Temperature Range	-55 – 125 °C [-67 – 257 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Rating	Listed
Compatible With Approved Standards Products	CSA 1195944, UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	8
Packaging Method	Box, Tube

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025
(247)
Candidate List Declared Against: JAN 2025
(247)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per
homogenous material. Also BFR/CFR/PVC
Free


Solder Process Capability

Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 5767127-4 MICT,PLG,152,ASY,.025,TAPE CAP	 TE Part # 1-5767127-1 MICT,PLG,152,ASY,.025,TAPE PKG	 TE Part # 5767039-4 MICTOR,RA PLUG,152,.093PCB,ASY	 TE Part # 5767006-4 MICT,R/APLUG,152,ASY,.025,.062
 TE Part # 5767042-4 MICT,738PLUG,152,ASSY,.025,EXT	 TE Part # 5767149-4 MICT,495,PLG,152,TAPE,CAP	 TE Part # 1-5767118-1 MICT,PLG,152,ASY,.025,TAPE PKG	 TE Part # 1-5767119-1 MICT,PLG,152,ASY,.025,TAPE PKG



TE Part # 5767025-4
MICTOR .707 PLUG ASSY, 152 POS



TE Part # 5767082-4
MICT,495,PLUG,152,PDNI,BARBLES



TE Part # 5767121-4
MICT,PLG,152,ASY,.025,TAPE CAP



TE Part # 1-5767149-1
MICTOR PLUG ASSY IN TAPE & REE



TE Part # 1-5767121-1
MICT,PLG,152,ASY,.025,TAPE PKG



TE Part # 5767111-4
MICT,PLG,152,ASY,.025 TAPE PKG



TE Part # 1-5767017-4
MICT,900PLUG,152,ASSY,.025,REC



TE Part # 5767032-4
MICT,788PLUG,152,ASSY,.025,REC



TE Part # 1-5767007-1
MICT,260PLUG,152,ASSY,.025,REC




TE Part # 5767055-4
MICT,R/APLUG,ASSY,152,PDNI

Customers Also Bought



TE Part #31428
TERMINAL,BUDG R 26-22 4




TE Part #202236-6
III+ PIN,SOLTAB,TIN,SMPAC



TE Part #200389-2
GUIDE PIN KIT



TE Part #200390-9
SERIES "M" GUIDE SOCKET



TE Part #5177983-4
0.8FH,R05H.5,100,08/Sn,TU



TE Part #5767055-1
MICT,R/APLUG,ASSY,38,PDNI



TE Part #200512-2
FEMALE BLOCK 26 PL.



TE Part #201359-1
MALE BLOCK 26 P. SER. "M"



Documents

Product Drawings

MICTOR RECEPT ASSY, 152 POS.

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-5767004-5_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-5767004-5_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-5767004-5_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

MICTOR Interconnection System

English

Fine Pitch Stacking Connectors - 0.635mm MICTOR Connectors

English

Product Specifications

Application Specification

English